



Global
Test Menu

Dimension EXL 200/ EXL with LM Integrated Chemistry Systems

Proven chemistry and immunoassay integration on a single system.

Dimension® EXL™ Integrated Chemistry Systems offer fast, easy-to-use versatility and proven outcomes.

- Delivers fast and reliable results using trusted, proven technologies including LOCI® advanced chemiluminescence.
- Frees up your staff with automated, productivity-enhancing features, including proactive alerts, STAT sample loading in any position, and single-tube simultaneous sampling for both chemistry and immunoassays.
- Provides a comprehensive menu with many critical laboratory assays.

The Dimension EXL with LM Integrated Chemistry System's Reagent Management System enables streamlined processing of a broad menu of chemistry and immunoassay tests with up to 91 assays on-board each system.

The Dimension EXL 200 Integrated Chemistry System's small size fits perfectly in STAT and small laboratories, and tests up to 47 assays at a time



Dimension EXL with LM Integrated Chemistry System



Dimension EXL 200 Integrated Chemistry System

Dimension EXL 200/EXL with LM Integrated Chemistry Systems

Global Test Menu

Anemia	General Chemistry	Immunosuppressant Drugs	Therapeutic Drug Monitoring (TDM)
Ferritin Folate Vitamin B12	Acid Phosphatase Alanine Aminotransferase (ALT) Albumin (BCP) Aldolase†‡ Alkaline Phosphatase (ALP) Ammonia Amylase Aspartate Aminotransferase Bilirubin, Direct Bilirubin, Total Calcium (CPC) Carbon Dioxide, Enzymatic Chloride Cholesterol Cholinesterase Creatinine Creatinine, Enzymatic Creatine Kinase Dibucaine Number†** Gamma Glutamyltransferase (GGT) Glucose HDL Cholesterol Hemolyzed Glucose†** Iron Lactate Lactate Dehydrogenase LDL Cholesterol Lipase Magnesium Microalbumin Pancreatic Amylase†‡ Phosphorus Potassium Pseudocholinesterase Sodium Total Iron Binding Capacity Total Protein Total Protein (CSF/Urine) Triglycerides Urea Nitrogen (BUN) Uric Acid	Cyclosporine§ Cyclosporine, Extended Range§ Everolimus†† Mycophenolic Acid Sirolimus§ Tacrolimus§	Amikacin** Caffeine** Carbamazepine Digitoxin Digoxin Gabapentin‡‡ Gentamicin Lamotrigine‡‡ Levetiracetam‡‡ Lidocaine Lithium Methotrexate** N-Acetylprocainamide (NAPA) Phenobarbital Phenytoin Procainamide Theophylline Tobramycin Topiramate‡‡ Valproic Acid Vancomycin Zonisamide‡‡
Bone Metabolism		Oncology	
Vitamin D Total		Free PSA Total PSA	
Cardiac		Reproductive Endocrinology	
BNP* CKMB Mass CardioPhase® hsCRP High-Sensitivity Troponin I† Myoglobin NT-proBNP† Troponin I		hCG	
Diabetes		Specific Proteins	
Fructosamine†‡ Hemoglobin A1c§		α1-Acid Glycoprotein†‡ β-2 Microglobulin Latex†‡ Antistreptolysin O (ASO)†‡ Apolipoprotein A-I†‡ Apolipoprotein B†‡ Ceruloplasmin†‡ Complement C3 Complement C4 CRP CRP, Extended Range Haptoglobin†‡ Immunoglobulin A Immunoglobulin G Immunoglobulin M Kappa light chains†‡ Lambda light chains†‡ Lipoprotein (a) Ultra†‡ Prealbumin Rheumatoid Factor (RF)†‡ Transferrin	
Drugs of Abuse/Toxicology		Thyroid	
6-Acetylmorphine (6-AM)** Acetaminophen Amphetamines Barbiturates, Urine Barbiturates, Serum** Benzodiazepines, Urine Benzodiazepines, Serum** Buprenorphine**†† Cannabinoids (THC) Cocaine Metabolite Ecstasy Ethyl Alcohol Methadone Methaqualone** Opiates Phencyclidine Propoxyphene** Salicylate Tricyclic Antidepressants**		Free T3 Free T4 T Uptake Total T4 TSH	

CardioPhase, Dimension, EXL, LOCI, and all associated marks are trademarks of Siemens Healthcare Diagnostics Inc., or its affiliates. All other trademarks and brands are the property of their respective owners.

Product availability may vary from country to country and is subject to varying regulatory requirements. Please contact your local representative for availability.

Siemens Healthineers Headquarters

Siemens Healthcare GmbH
Henkestr. 127
91052 Erlangen, Germany
Phone: +49 9131 84-0
siemens-healthineers.com

Published by

Siemens Healthcare Diagnostics Inc.
Laboratory Diagnostics
511 Benedict Avenue
Tarrytown, NY 10591-5005
USA
Phone: +1 914-631-8000