



## Global Test Menu

# Dimension EXL 200/EXL with LM Integrated Chemistry Systems

Proven chemistry and immunoassay integration on a single system.

Dimension® EXL™ Integrated Chemistry Systems offer fast, easy-to-use versatility and proven outcomes.

- Deliver fast and reliable results using trusted, proven technologies including LOCI® advanced chemiluminescence.
- Free up your staff with automated, productivity-enhancing features, including proactive alerts, STAT sample loading in any position, and single-tube simultaneous sampling for both chemistry and immunoassays.
- Provide a comprehensive menu with many critical laboratory assays.

The Dimension EXL with LM Integrated Chemistry System's Reagent Management System enables streamlined processing of a broad menu of chemistry and immunoassay tests, with up to 91 assays onboard each system.

The Dimension EXL 200 Integrated Chemistry System fits perfectly in STAT and small laboratories and tests up to 47 assays at a time.

[siemens-healthineers.com](http://siemens-healthineers.com)



Dimension EXL with LM Integrated Chemistry System



Dimension EXL 200 Integrated Chemistry System

# Dimension EXL 200/EXL with LM Integrated Chemistry Systems

## Global Test Menu

<b>Anemia</b> Ferritin Folate Vitamin B12	<b>General Chemistry</b> Acid Phosphatase Alanine Aminotransferase (ALT) Albumin (BCP) Aldolase†,‡ Alkaline Phosphatase (ALP) Ammonia Amylase Aspartate Aminotransferase Bilirubin, Direct Bilirubin, Total Calcium (CPC) Carbon Dioxide Chloride Cholesterol Creatinine Creatinine (Enzymatic) Creatine Kinase Dibucaine Number†,‡ Gamma Glutamyltransferase (GGT) Glucose Glucose, Hemolyzed†,‡ HDL Cholesterol Iron Lactate Lactate Dehydrogenase LDL Cholesterol Lipase Magnesium Microalbumin Pancreatic Amylase†,‡ Phosphorus Potassium Pseudocholesterase Sodium Total Iron Binding Capacity Total Protein Total Protein, CSF/Urine Triglycerides Urea Nitrogen (BUN) Uric Acid	<b>Immunosuppressant Drugs</b> Cyclosporine <sup>§</sup> Cyclosporine, Extended Range <sup>§</sup> Everolimus†† Mycophenolic Acid Sirolimus <sup>§</sup> Tacrolimus <sup>§</sup>	<b>Therapeutic Drug Monitoring (TDM)</b> Amikacin** Caffeine** Carbamazepine Digitoxin Digoxin Ethosuximide** Gentamicin Lidocaine Lithium Methotrexate** N-Acetylprocainamide (NAPA) Phenobarbital Phenytoin Procainamide Theophylline Tobramycin Valproic Acid Vancomycin
<b>Bone Metabolism</b> Vitamin D Total		<b>Oncology</b> Free PSA Total PSA	
<b>Cardiac</b> BNP* CKMB Mass CardioPhase® hsCRP High-Sensitivity Troponin I Myoglobin NT-proBNP Troponin I		<b>Reproductive Endocrinology</b> hCG	
<b>Diabetes</b> Fructosamine†,‡ Hemoglobin A1c <sup>§</sup>		<b>Specific Proteins</b> α1-Acid Glycoprotein†,‡ β-2 Microglobulin Latex†,‡ Antistreptolysin O (ASO)†,‡ Apolipoprotein A-I†,‡ Apolipoprotein B†,‡ Ceruloplasmin†,‡ Complement C3 Complement C4 CRP CRP, Extended Range Haptoglobin†,‡ Ig Light Chains, Type Kappa†,‡ Ig Light Chains, Type Lambda†,‡ Immunoglobulin A Immunoglobulin G Immunoglobulin M Lipoprotein(a) Ultra†,‡ Prealbumin Rheumatoid Factor (RF)†,‡ Transferrin	<b>Thyroid</b> Free T3 Free T4 T Uptake Total T4 TSH
<b>Drugs of Abuse/Toxicology</b> 6-Acetylmorphine (6-AM)** Acetaminophen Amphetamines Barbiturates, Urine Barbiturates, Serum** Benzodiazepines, Urine Benzodiazepines, Serum** Buprenorphine** Cannabinoids (THC) Cocaine Metabolite Ecstasy Ethyl Alcohol Fentanyl††,‡‡ Methadone Methaqualone** Opiates Oxycodone** Phencyclidine Propoxyphene** Salicylate Tricyclic Antidepressants**			

\* Available for sale only in Japan.  
 † Not available for sale in the U.S.  
 ‡ Alliance Application manufactured by third party, distributed by Siemens Healthcare Diagnostics.  
 § No manual pretreatment.  
 \*\* Alliance Application manufactured and distributed by Siemens Healthcare Diagnostics.  
 †† Under development.  
 ‡‡ Not available for sale.  
 ‡‡ Manufactured by third party, distributed by Siemens Healthcare Diagnostics.

CardioPhase, Dimension, EXL, LOCI, and all associated marks are trademarks of Siemens Healthcare Diagnostics Inc., or its affiliates. All other trademarks and brands are the property of their respective owners.

Product availability may vary from country to country and is subject to varying regulatory requirements. Please contact your local representative for availability.

**Siemens Healthineers Headquarters**  
 Siemens Healthcare GmbH  
 Henkestr. 127  
 91052 Erlangen, Germany  
 Phone: +49 9131 84-0  
 siemens-healthineers.com

**Published by**  
 Siemens Healthcare Diagnostics Inc.  
 Laboratory Diagnostics  
 511 Benedict Avenue  
 Tarrytown, NY 10591-5005  
 USA  
 Phone: +1 914-631-8000