



For use
outside
the U.S.

Atellica Solution

Test Menu

Flexible, scalable, automation-ready immunoassay and clinical chemistry analyzers engineered to deliver control and simplicity so you can drive better outcomes

Experience the power of the Atellica® Solution, featuring patented bidirectional magnetic sample transport technology, the flexibility to create over 300 customizable configurations, and a broad assay menu with proven detection technologies.

Chemistry

Diabetes

- Fructosamine
- Hemoglobin A1c

Drugs of Abuse/Toxicology

- 6-Acetylmorphine (6-AM)*
- Acetaminophen
- Amphetamines
- Barbiturates, Urine
- Barbiturates, Serum*
- Benzodiazepines, Urine
- Benzodiazepines, Serum*
- Buprenorphine*
- Cannabinoids (THC)
- Cocaine Metabolite
- Ecstasy
- Ethyl Alcohol
- Methadone
- Methadone Metabolite (EDDP)
- Opiates
- Phencyclidine
- Propoxyphene
- Salicylate
- Tricyclic Antidepressants*

General Chemistry

- Alanine Aminotransferase (ALT)
- Alanine Aminotransferase (Liquid PSP)
- Albumin (BCG)
- Albumin (BCP)
- Alkaline Phosphatase
- Ammonia
- Amylase
- Aspartate Aminotransferase (AST)
- Aspartate Aminotransferase (Liquid PSP)
- Bilirubin, Direct
- Bilirubin, Total
- Calcium (CPC)
- Carbon Dioxide
- Chloride
- Cholesterol
- Cholinesterase
- Creatine Kinase
- Creatinine
- Creatinine, Enzymatic
- Gamma-Glutamyl Transferase (GGT)
- Glucose, Hexokinase
- Glucose, Oxidase
- HDL Cholesterol
- Iron
- Lactate
- Lactate Dehydrogenase (L-P)

- LDL Cholesterol
- Lipase
- Magnesium
- Microalbumin
- Pancreatic Amylase
- Phosphorus
- Potassium
- Sodium
- Total Iron Binding Capacity (TIBC)
- Total Protein
- Total Protein, Urine
- Triglycerides
- Urea Nitrogen (BUN)
- Uric Acid

Specific Proteins

- α1-Acid Glycoprotein (AAG)
- α1-Antitrypsin (AAT)
- Antistreptolysin O (ASO)
- Apolipoprotein A-1
- Apolipoprotein B
- β-2 Microglobulin
- Complement C3
- Complement C4
- CRP
- CRP, High Sensitivity
- CRP, Wide Range†
- Cystatin C†
- FLC kappa††
- FLC lambda††

- Haptoglobin
- Immunoglobulin A (IgA)
- Immunoglobulin G (IgG)
- Immunoglobulin M (IgM)
- Lipoprotein(a)
- Prealbumin
- Rheumatoid Factor (RF)
- Soluble Transferrin Receptor (sTfR)††
- Transferrin

Therapeutic Drug Monitoring

- Caffeine*
- Carbamazepine
- Digoxin
- Gentamicin
- Lithium
- Methotrexate*
- Phenobarbital
- Phenytoin
- Theophylline
- Tobramycin
- Valproic Acid
- Vancomycin

*Alliance application.

†Under development. Not commercially available. Future availability cannot be guaranteed.

Atellica Portfolio of Laboratory Products

Engineered by Siemens Healthineers to deliver control and simplicity so you can drive better outcomes.

Tighter control of your lab, simplified workflow, and more time to focus on driving better business and clinical outcomes—that's the promise of our Atellica® portfolio of laboratory products.

Control. Simplicity. Better Outcomes.

Atellica Solution Test Menu



Immunoassay

Anemia

Active-B12†
EPO†
Ferritin
Folate
RBC Folate
Vitamin B12

Autoimmune

Anti-CCP†

Bone Metabolism

Intact PTH
Vitamin D Total

Cardiac

BNP
CKMB
High-Sensitivity Troponin I (TNIH)
Myoglobin
NT-proBNP
TnI-Ultra™

Diabetes

C-Peptide
Insulin

Growth

Growth Hormone (hGH)†
IGFBP-3†
IGF-I†

Hepatitis

Anti-HBe
Anti-HBs 2
HAV IgM
HAV Total
HBc IgM
HBc Total
HBeAg
HBsAg II
HBsAg II Quant†
HBsAg Confirmatory
HCV‡

HIV

HIV 1/0/2 Enhanced (EHIV)‡
HIV Ag/Ab Combo (CHIV)‡

Immunosuppressant Drugs

Cyclosporine
Everolimus†

Inflammation

IgE, Total
IL-6†
LBP†

Liver Fibrosis

Enhanced Liver Fibrosis (ELF™) Test
HA (ELF Marker)
PIIINP (ELF Marker)
TIMP-1 (ELF Marker)

Metabolic

ACTH†
Cortisol
Homocysteine

Oncology

AFP
BR 27.29
CA 125II
CA 15-3
CA 19-9
Calcitonin†
CEA
Complexed PSA
Free PSA
PSA
Serum HER-2/neu

Reproductive Endocrinology

Androstenedione†
Anti-Mullerian Hormone (AMH)†
DHEAS
Enhanced Estradiol
Free β-hCG†
FSH
hCG
LH
PAPP-A†
PLGF†
Progesterone
Prolactin
sFLT-1†
SHBG
Testosterone II

Sepsis

Procalcitonin (PCT)

Special ID

EBV-EBNA IgG†
EBV-VCA IgG†
EBV-VCA IgM†
Syphilis

Therapeutic Drug Monitoring

Digitoxin
Digoxin

Thyroid

Anti-TG
Anti-TPO
Free T3
Free T4
Thyroglobulin (Tg)†
Total T3
Total T4
TSH3-Ultra
T Uptake

ToRCH

CMV IgG†
CMV IgM†
Herpes 1†
Herpes 2†
Rubella IgG
Rubella IgM
Toxoplasma IgG
Toxoplasma IgM

For use
outside
the U.S.

†Under development. Not commercially available. Future availability cannot be guaranteed.

‡Assay developed, manufactured, and sold by Siemens Healthcare Diagnostics Inc. for Ortho Clinical Diagnostics, Inc. and Grifols Diagnostic Solutions Inc.

Atellica, ELF, TnI-Ultra, and all associated marks are trademarks of Siemens Healthcare Diagnostics Inc., or its affiliates. All other trademarks and brands are the property of their respective owners.

Product availability may vary from country to country and is subject to varying regulatory requirements. Please contact your local representative for availability.

Siemens Healthineers

Headquarters

Siemens Healthcare GmbH
Henkestr. 127
91052 Erlangen
Germany
Phone: +49 9131 84 0
siemens.com/healthineers

Local Contact Information

Siemens Healthcare Diagnostics Inc.
Laboratory Diagnostics
511 Benedict Avenue
Tarrytown, NY 10591-5005
USA
Phone: +1 914-631-8000