



Global
Test Menu

ADVIA Centaur XPT/XP/CP Immunoassay Systems

Siemens Healthineers unites innovative workflow solutions with clinical excellence in the ADVIA Centaur® family of systems, leading to greater laboratory productivity to stay ahead of increasing workload demands.

- Provides sensitivity and specificity you expect of chemiluminescence with Advanced Acridinium Ester Technology
- Increases productivity by connecting to Siemens Healthineers Aptio® Automation and VersaCell® Solutions
- Utilizes the same ready-to-use reagents are used across all ADVIA Centaur Systems

ADVIA Centaur XPT System

Designed with one of the most advanced software packages on the market, the ADVIA Centaur® XPT System is among the highest-throughput systems available. The ADVIA Centaur XPT System delivers the results that clinicians depend upon for accurate diagnoses and better patient care—and does so predictably and consistently.

ADVIA Centaur XP System

The high-performance ADVIA Centaur® XP System has extensive onboard reagent capacity and dedicated STAT capabilities to maximize productivity, regardless of volume or types of tests. Always ready, continuous operation to keep pace with peak workload time.

ADVIA Centaur CP System

The ADVIA Centaur® CP System is a mid-volume, high-throughput benchtop system that enhances your in-house test capabilities. With its broad menu and short turnaround times, you can do more—without compromising efficiency, productivity, or quality.



ADVIA Centaur XPT System



ADVIA Centaur XP System



ADVIA Centaur CP System

ADVIA Centaur XPT/XP/CP Immunoassay Systems

Global Test Menu

◆ ADVIA Centaur® XPT System

▲ ADVIA Centaur® XP System

● ADVIA Centaur® CP System

Allergy	Hepatitis	Metabolic	Sepsis
◆ ▲ ● IgE, Total	◆† ▲† ●† HBeAb	◆* ▲* ●* ACTH	◆† ▲† ●† Procalcitonin
	◆ ▲ ● HBsAb 2	◆ ▲ ● Cortisol	
Anemia	◆ ▲ ● HAV IgM	◆ ▲ ● Homocysteine	Special ID
◆ ▲ ●* Active-B12	◆ ▲ ● HAV Total		◆* ▲* ●* <i>H. pylori</i> IgG
◆† ▲† ●* EPO	◆ ▲ ● HBc IgM	Oncology	◆ ▲ ● Syphilis
◆ ▲ ● Ferritin	◆ ▲ ● HBc Total	◆† ▲ ▲ ● AFP	
◆ ▲ ● Folate	◆ ▲ ● HBeAg	◆ ▲ ● BR 27.29	
◆ ▲ ● RBC Folate	◆† ▲† ●† HBsAgII	◆ ▲ ● CA 125II	
◆ ▲ ● Vitamin B12	◆† ▲† ●† HBsAgII Quant	◆ ▲ ● CA 15-3	
	◆ ▲ ● HBsAg	◆ ▲ ● CA 19-9	
Autoimmune	◆ ▲ ● HBsAg Confirmatory	◆* ▲* ●* Calcitonin	
◆ ▲ ● Anti-CCP	◆* ▲* ●* HCV	◆ ▲ ● CEA	
	HIV	◆ ▲ ● Complexed PSA	
	◆* ▲* ●* HIV 1/O/2 Enhanced (EHIV)	◆† ▲† ● Free PSA	
	◆* ▲* ●* HIV Combo (CHIV)	◆ ▲ ● PSA	
		◆ ▲ ● Serum HER-2/neu	
Bone Metabolism		Reproductive Endocrinology	
◆ ▲ ● Intact PTH		◆† ▲ ▲ ● AFP	
◆ ▲ ●* Vitamin D Total		◆* ▲* ●* Anti-Müllerian Hormone	
	Immunosuppressant Drugs	◆ ▲ ● DHEAS	
	◆ ▲ ● Cyclosporine	◆ ▲ ● Enhanced Estradiol	
	◆* ▲* ●* Everolimus	◆* ▲* ●* Free βhCG	
	◆* ▲* ●* Sirolimus	◆ ▲ ● FSH	
	◆* ▲* ●* Tacrolimus	◆ ▲ ● hCG	
	Inflammation	◆ ▲ ● LH	
	◆* ▲* ●* IL-6	◆* ▲* ●* PAPP-A	
	◆* ▲* ●* LBP	◆* ▲* ●* PIGF	
	Liver Fibrosis	◆ ▲ ● Progesterone	
	◆† ▲† ●† Enhanced Liver Fibrosis (ELF™) Test	◆ ▲ ● Prolactin	
	◆† ▲† ●† HA (ELF™ Marker)	◆* ▲* ●* sFLT-1	
	◆† ▲† ●† PIIINP (ELF™ Marker)	◆ ▲ ● SHBG	
	◆† ▲† ●† TIMP (ELF™ Marker)	◆ ▲ ● Testosterone II	
Cardiac		Thyroid	
◆ ▲ ● BNP		◆ ▲ ● Anti-Tg	
◆ ▲ ● CKMB		◆ ▲ ● Anti-TPO	
◆* ▲* ●* Galectin-3		◆ ▲ ● Free T3	
◆† ▲† ●* High-Sensitivity Troponin I (TNIH)		◆ ▲ ● Free T4	
◆ ▲ ● Myoglobin		◆ ▲ ● T Uptake	
◆† ▲† ●† NT-proBNP		◆ ▲ ● Total T3	
◆ ▲ ● TnI-Ultra™		◆ ▲ ● Total T4	
		◆ ▲ ● TSH3-Ultra	
		◆ ▲ ● TSH	
Diabetes		ToRCH	
◆ ▲ ● C-Peptide		◆* ▲* ●* CMV IgG	
◆ ▲ ● Insulin		◆* ▲* ●* CMV IgM	
		◆† ▲† ●† Herpes-1 IgG	
		◆† ▲† ●† Herpes-2 IgG	
		◆ ▲ ● Rubella IgG	
		◆ ▲ ● Rubella IgM	
		◆ ▲ ● Toxoplasma IgG	
		◆ ▲ ●* Toxoplasma IgM	

*Under development. Not available for sale.

†Not available for sale in the U.S.

‡Not CE marked.

§The ADVIA Centaur HCV and HIV assays are developed, manufactured and sold by Siemens for Ortho-Clinical Diagnostics, Inc. and Grifols Diagnostic Solutions Inc.

ADVIA, ADVIA Centaur, Aptio, ELF, TnI-Ultra, VersaCell, and all associated marks are trademarks of Siemens Healthcare Diagnostics Inc., or its affiliates. All other trademarks and brands are the property of their respective owners.

Product availability may vary from country to country and is subject to varying regulatory requirements. Please contact your local representative for availability.

Siemens Healthineers Headquarters

Siemens Healthcare GmbH
Henkestr. 127
91052 Erlangen, Germany
Phone: +49 9131 84-0
siemens.com/healthineers

Published by

Siemens Healthcare Diagnostics Inc.
Laboratory Diagnostics
511 Benedict Avenue
Tarrytown, NY 10591-5005
USA
Phone: +1 914-631-8000