



For use
outside
the U.S.

Atellica Solution

Test Menu

Flexible, scalable, automation-ready immunoassay and clinical chemistry analyzers engineered to deliver control and simplicity so you can drive better outcomes

Experience the power of the Atellica® Solution, featuring patented bidirectional magnetic sample transport technology, the flexibility to create over 300 customizable configurations, and a broad assay menu with proven detection technologies.

Chemistry

Diabetes

- Fructosamine
- Hemoglobin A1c

Drugs of Abuse/Toxicology

- 6-Acetylmorphine (6-AM)*
- Acetaminophen
- Amphetamines
- Barbiturates, Urine
- Barbiturates, Serum*
- Benzodiazepines, Urine
- Benzodiazepines, Serum*
- Buprenorphine*
- Cannabinoids (THC)
- Cocaine Metabolite
- Ecstasy
- Ethyl Alcohol
- Ethyl Glucuronide†
- LSD*
- Methadone
- Methadone Metabolite (EDDP)
- Methaqualone*
- Opiates
- Oxycodone
- Phencyclidine
- Propoxyphene
- Salicylate
- Tricyclic Antidepressants*

General Chemistry

- Alanine Aminotransferase (ALT)
- Alanine Aminotransferase (PSP)
- Albumin (BCG)
- Albumin (BCP)
- Alkaline Phosphatase
- Ammonia
- Amylase
- Aspartate Aminotransferase (AST)
- Aspartate Aminotransferase (PSP)
- Bilirubin, Direct
- Bilirubin, Total
- Calcium (Arsenazo)
- Calcium (CPC)
- Carbon Dioxide Chloride
- Cholesterol
- Cholinesterase
- Creatine Kinase
- Creatinine
- Creatinine (Enzymatic)
- Gamma-Glutamyl Transferase (GGT)
- Glucose (Hexokinase)
- Glucose (Oxidase)
- HDL Cholesterol
- Iron
- Lactate
- Lactate Dehydrogenase (L-P)
- LDL Cholesterol
- Lipase

- Magnesium
- Microalbumin
- Pancreatic Amylase
- Phosphorus
- Potassium
- Sodium
- Total Iron Binding Capacity (TIBC)
- Total Protein
- Total Protein, Urine
- Triglycerides
- Urea Nitrogen (BUN)
- Uric Acid

Immunosuppressant Drugs

- Mycophenolic Acid
- Tacrolimus

Specific Proteins

- α1-Acid Glycoprotein (AAG)
- α1-Antitrypsin (AAT)
- Antistreptolysin O (ASO)
- Apolipoprotein A-1
- Apolipoprotein B
- β-2 Microglobulin
- Ceruloplasmin†
- Complement C3
- Complement C4
- CRP
- CRP, High Sensitivity
- CRP, Wide Range
- Cystatin C
- Free Light Chain kappa*
- Free Light Chain lambda*

- Haptoglobin
- Immunoglobulin A (IgA)
- Immunoglobulin G (IgG)
- Immunoglobulin M (IgM)
- Lipoprotein(a)
- Prealbumin
- Rheumatoid Factor (RF)
- Soluble Transferrin Receptor (sTfR)†
- Transferrin

Specimen Validity Testing

- Creatinine*
- Nitrite*
- Oxidant*
- pH*
- Specific Gravity*

Therapeutic Drug Monitoring

- Amikacin*
- Caffeine*
- Carbamazepine
- Digoxin
- Gentamicin
- Lidocaine
- Lithium
- Methotrexate†
- N-Acetylprocainamide (NAPA)
- Phenobarbital
- Phenytoin
- Procainamide
- Theophylline
- Tobramycin
- Valproic Acid
- Vancomycin

*Alliance application manufactured and distributed by Siemens Healthcare Diagnostics Inc.
†Alliance application manufactured by third party, distributed by Siemens Healthcare Diagnostics Inc.

Atellica Portfolio of Laboratory Products

Engineered by Siemens Healthineers to deliver control and simplicity so you can drive better outcomes.

Tighter control of your lab, simplified workflow, and more time to focus on driving better business and clinical outcomes—that's the promise of our Atellica® portfolio of laboratory products.

Control. Simplicity. Better Outcomes.

Atellica Solution Test Menu



Immunoassay

Anemia

Active-B12
EPO
Ferritin
Folate
RBC Folate
Vitamin B12

Autoimmune

Anti-CCP

Bone Metabolism

Intact PTH
Vitamin D Total

Cardiac

BNP
CKMB
High-Sensitivity Troponin I (TnIH)
Myoglobin
NT-proBNP
TnI-Ultra®

Diabetes

C-Peptide
Insulin

Growth

Growth Hormone (hGH)[‡]
IGFBP-3[‡]
IGF-1[‡]

Hepatitis

Anti-HBe
Anti-HBs 2
HAV IgM
HAV Total
HBc IgM
HBc Total
HBeAg
HBsAg II
HBsAg II Quant[‡]
HBsAg Confirmatory
HCV[§]

HIV

HIV 1/O/2 Enhanced (EHIV)^{**}
HIV Ag/Ab Combo (CHIV)^{**}

Immunosuppressant Drugs

Cyclosporine
Everolimus[‡]
Sirolimus[‡]

Inflammation

IgE, Total
IL-6[‡]
LBP[‡]

Liver Fibrosis

Enhanced Liver Fibrosis (ELF™) Test
HA (ELF Test)
PIIINP (ELF Test)
TIMP-1 (ELF Test)

Metabolic

ACTH[‡]
Cortisol
Homocysteine

Oncology

AFP
BR 27.29
CA 125II™††
CA 15-3
CA 19-9
Calcitonin
CEA
Complexed PSA
Free PSA
PSA
Serum HER-2/neu

Reproductive Endocrinology

Androstenedione[‡]
Anti-Mullerian Hormone (AMH)[‡]
DHEAS
Enhanced Estradiol
Free β-hCG
FSH
hCG
LH
PAPP-A
PLGF[‡]
Progesterone
Prolactin
sFLT-1[‡]
SHBG
Testosterone II

Sepsis

Procalcitonin (PCT)

Special ID

EBV-EBNA IgG[‡]
EBV-VCA IgG[‡]
EBV-VCA IgM[‡]
Syphilis

Therapeutic Drug Monitoring

Digitoxin
Digoxin

Thyroid

Anti-TG
Anti-TPO
Free T3
Free T4
Thyroglobulin (Tg)[‡]
Total T3
Total T4
TSH3-Ultra
T Uptake

ToRCH

CMV IgG
CMV IgM[‡]
Herpes-1 IgG[‡]
Herpes-2 IgG[‡]
Rubella IgG
Rubella IgM
Toxoplasma IgG
Toxoplasma IgM

For use
outside
the U.S.

[‡]Under development. Not commercially available. Future availability cannot be guaranteed.

[§]For outside the U.S. only, assay developed, manufactured, and sold by Siemens Healthcare Diagnostics Inc.

for Ortho Clinical Diagnostics, Inc. and Grifols Diagnostic Solutions Inc.

^{**}Assay developed, manufactured, and sold by Siemens Healthcare Diagnostics Inc. for Ortho Clinical Diagnostics, Inc. and Grifols Diagnostic Solutions Inc.

^{††}CA 125II is a trademark of Fujirebio Diagnostics, Inc.

Atellica, ELF, TnI-Ultra, and all associated marks are trademarks of Siemens Healthcare Diagnostics Inc., or its affiliates. All other trademarks and brands are the property of their respective owners.

Product availability may vary from country to country and is subject to varying regulatory requirements. Please contact your local representative for availability.

Siemens Healthineers Headquarters

Siemens Healthcare GmbH
Henkestr. 127
91052 Erlangen, Germany
Phone: +49 9131 84-0
siemens-healthineers.com

Published by

Siemens Healthcare Diagnostics Inc.
Laboratory Diagnostics
511 Benedict Avenue
Tarrytown, NY 10591-5005
USA
Phone: +1 914-631-8000