

Chemistry and Immunoassay Menu

For use
outside the
U.S. only

Assay	Atellica® Solution	ADVIA Centaur® XP/ XPT Systems	ADVIA Centaur® CP System	ADVIA® Chemistry Systems	Dimension Vista® Systems	Dimension® EXL® Systems	IMMULITE® 2000/2000 XPI Systems	IMMULITE® 1000 System
6-Acetylmorphine (6-AM)	• ⁷			• ⁷	• ⁷	• ⁷		
α1-Acid Glycoprotein	•			•	•	• ^{2,6}		
α1-Antitrypsin (AAT)	•			•	•			
α1-Microglobulin					•			
α2-Macroglobulin					•			
Acetaminophen	•			•	•	•		
Acid Phosphatase						•		
ACTH	• ¹	• ¹	• ¹				•	•
Active-B12	• ¹	•	• ¹					
Aldolase					• ^{2,6}	• ^{2,6}		
AFP	•	•	•		•		•	• ²
Alanine Aminotransferase (ALT)	•			• ⁴				
Alanine Aminotransferase (PSP)	•			• ⁴	•	•		
AlaTOP Allergy Screen							• ²	• ²
Albumin (BCG)	•			• ⁴				
Albumin (BCP)	•			•	•	•		
Albumin, Nephelometry					•			
Alkaline Phosphatase	•			• ⁵	•	•		
Alkaline Phosphatase (DEA)				• ²				
Allergen-Specific IgE 3gAllergy™							•	
Allergen-Specific IgG							• ²	
Allergen-Specific IgG4							• ²	
AMH (Anti-Müllerian Hormone)	• ¹	• ¹	• ¹					
Amikacin					• ⁷	• ⁷		
Ammonia	•			•	•	•		
Amphetamines	•			•	•	•		
Amylase	•			•	•	•		
Androstenedione	• ¹	• ¹	• ¹				•	•
Anti-CCP	• ¹	•	•				•	
Antistreptolysin O (ASO)	•			•	•	• ^{2,6}		
Anti-HBe	• ²	• ²	• ²					
Anti-HBs	• ²	•	• ²				•	
Anti-TG	•	•	•				•	•
Anti-TPO	•	•	•				•	•
Apolipoprotein A-I	•			•	•	• ^{2,6}		
Apolipoprotein B	•			•	•	• ^{2,6}		
Aspartate Aminotransferase	•			• ⁴				
Aspartate Aminotransferase (PSP)	•			• ⁴	•	•		
β-2 Microglobulin	•			•	•	• ^{2,6}	•	•
Barbiturates, Serum	• ⁷			•	• ⁷	• ⁷		

Assay	Atellica Solution	ADVIA Centaur XP/XPT Systems	ADVIA Centaur CP System	ADVIA Chemistry Systems	Dimension Vista Systems	Dimension EXL Systems	IMMULITE 2000/2000 XPI Systems	IMMULITE 1000 System
Barbiturates, Urine	●			●	●	●	●	●
Benzodiazepines, Serum	● ⁷			●	● ⁷	● ⁷		
Benzodiazepines, Urine	●			●	●	●		
Bilirubin, Direct	●			●	●	●		
Bilirubin, Total	●			●	●	●		
BNP	●	●	●		● ²	● ^{2,12}		
BR 27.29	●	●	●					
Buprenorphine	● ⁷			● ¹	● ¹	● ¹		
C-Peptide	●	●	●				●	●
C1 Inhibitor					●			
CA 125II (OM-MA)	●	●	●		●		●	●
CA 15-3 (BR-MA)	●	●	●		●		●	●
CA 19-9 (GI-MA)	●	●	●		●		● ²	● ²
Caffeine	● ⁷				● ⁷	● ⁷		
Calcitonin	● ¹	● ²	● ¹				●	●
Calcium (Arsenazo)	● ¹			● ⁴				
Calcium (CPC)	●			● ⁴	●	●		
Canine Free T4							●	●
Canine TLI							●	●
Canine Total T4							●	●
Canine TSH							●	●
Cannabinoids (THC)	●			●	●	●		
Carbamazepine	●	●	●	●	●	●	●	●
Carbon Dioxide, Enzymatic	●			● ⁵	●	●		
CEA	●	●	●		●		●	●
Ceruloplasmin	● ^{1,6}				●	● ^{2,6}		
Chloride	●			●	●	●		
Cholesterol	●			● ⁴	●	●		
Cholinesterase	●			●				
CKMB	●	●	●		●	●	● ²	● ²
CKMB Mass					●	●	●	●
CMV IgG	● ¹	● ¹	● ¹				●	●
CMV IgM	● ¹	● ¹	● ¹				●	●
Cocaine Metabolite	●			●	●	●		
Complement C3	●			●	●	●		
Complement C4	●			●	●	●		
Complexed PSA	● ²	●	●					
Cortisol	●	●	●				●	●
Creatine Kinase	●			●	●	●		
Creatinine	●			● ⁴	●	●		
Creatinine, Enzymatic	●			●	●	●		
Creatinine Validity Test				● ^{3,7,10}				
CRP	●			●	●	●		
CRP, High Sensitivity	●			●	●	●	●	●
CRP, Wide Range	● ¹			●		●		
Cyclosporine	●	●	●		● ⁸	● ⁸		
Cyclosporine, Extended Range					● ⁸	● ⁸		
Cystatin C	● ¹			●	●			
D-Dimer							● ²	● ²
DHEAS	●	●	●				●	●
Dibucaine Number						● ^{2,7}		
Digitoxin	●	●	●		●	●	●	
Digoxin	●	●	●	●	●	●	●	● ²
EBV-EBNA IgG	● ¹	● ¹	● ¹				● ²	
EBV-VCA IgG	● ¹	● ¹	● ¹				● ²	

Assay	Atellica Solution	ADVIA Centaur XP/XPT Systems	ADVIA Centaur CP System	ADVIA Chemistry Systems	Dimension Vista Systems	Dimension EXL Systems	IMMULITE 2000/2000 XPI Systems	IMMULITE 1000 System
EBV-VCA IgM	● ¹	● ¹	● ¹				● ²	
ECP							● ²	● ²
Ecstasy	●			●	●	●		
Enhanced Estradiol	●	●	●					
Enhanced Liver Fibrosis (ELF™) Test	● ²	● ²	● ²					
EPO	● ¹	● ²	● ¹				● ²	● ²
Estradiol					●		●	●
Ethyl Alcohol	●			●	●	●		
Everolimus	● ¹	● ¹	● ¹			● ¹		
Fentanyl	● ¹			● ¹	●	● ¹		
Ferritin	●	●	●	●	●	●	●	●
Folate	●	●	●				●	
Free βHCG	● ¹	● ¹	● ¹				● ²	● ²
Free PSA	● ²	● ²	● ²		●	●	●	●
Free T3	●	●	●		●	●	●	●
Free T4	●	●	●		●	●	●	●
Fructosamine	●			●	● ^{2,6}	● ^{2,6}		
FSH	●	●	●		●		●	●
Gabapentin				● ⁶	● ⁶	● ⁶		
Gamma Glutamyltransferase (GGT)	●			●	●	●		
Gastrin							●	●
Gentamicin	●	●	●	●	●	●		
Glucose, Hexokinase	●			● ⁴	●	●		
Glucose, Oxidase	●			● ⁴				
Growth Hormone (hGH)	● ¹	● ¹	● ¹				●	●
<i>H. pylori</i> IgG							●	●
HA (ELF™ Test)	● ²	● ²	● ²					
Haptoglobin	●			●	●	● ^{2,6}		
HAV IgM	●	●	●					
HAV Total	●	●	●					
HbC IgM	● ²	●	●				●	
HbC Total	● ²	●	●				●	
HBeAg	● ²	●						
HBsAg		● ^{9,11}	● ¹¹				●	
HBsAg Confirmatory	● ²	●	●				●	
HBsAg II	● ²	●	● ²					
hCG	●	●	●		●	●	●	●
HCV	● ^{2,13}	● ¹³	● ¹³					
HDL Cholesterol	●			●	●	●		
Hemoglobin A1c	● ⁸			● ⁸	● ⁸	● ⁸		
Hemolyzed Glucose					● ^{2,7}	● ^{2,7}		
Hemopexin					●			
Herpes I and II IgG							●	●
Herpes-1 IgG	● ¹	● ²	● ²					
Herpes-2 IgG	● ¹	● ²	● ²					
HIV 1/O/2 Enhanced (EHIV)	● ^{2,13}	● ¹³	● ¹³					
HIV Ag/Ab Combo (CHIV)	● ^{2,13}	● ¹³	● ¹³					
Homocysteine	●	●	●		●		●	●
Ig Light Chains, Type Kappa	● ^{1,7}				●	● ^{2,6}		
Ig Light Chains, Type Lambda	● ^{1,7}				●	● ^{2,6}		
IgE, Total	●	●	●				●	●
IGF-I	● ¹	● ¹	● ¹				●	●
IGFBP-3	● ¹	● ¹	● ¹				●	
IgG Subclasses 1–4					●			
IL-1B							● ²	

Assay	Atellica Solution	ADVIA Centaur XP/ XPT Systems	ADVIA Centaur CP System	ADVIA Chemistry Systems	Dimension Vista Systems	Dimension EXL Systems	IMMULITE 2000/2000 XPI Systems	IMMULITE 1000 System
IL-10							● ²	
IL-2R							● ²	● ²
IL6	● ¹	● ²	● ¹				● ²	● ²
IL-8							● ²	
Immunoglobulin A (IgA)	●			●	●	●		
Immunoglobulin E (IgE)	●	●	●		●			
Immunoglobulin G (IgG)	●			●	●	●		
Immunoglobulin M (IgM)	●			●	●	●		
Insulin	●	●	●				●	●
Intact PTH	●	●	●				●	●
Iron	●			●	●	●		
Lactate	●			●	●	●		
Lactate Dehydrogenase (L-P)	●			●	●	●		
Lactate Dehydrogenase (P-L)				●				
Lamotrigine				● ⁶	● ⁶	● ⁶		
Levetiracetam				● ⁶	● ⁶	● ⁶		
LBP	● ¹	● ²	● ¹				● ²	● ²
LDL Cholesterol	●			●	●	●		
LH	●	●	●		●		●	●
Lidocaine					●	●		
Lipase	●			●	●	●		
Lipoprotein(a)	●			●	● ^{2,6}	● ^{2,6}		
Lithium	●			●	●	●		
Magnesium	●			● ⁴	●	●		
Methadone	●			●	●	●		
Methadone Metabolites (EDDP)	●			●				
Methaqualone					● ⁷	● ⁷		
Methotrexate	● ⁶			● ⁶	● ⁶	● ⁷		
Microalbumin	●			●	●	●	●	●
Mycophenolic Acid (MPA)	● ¹					●		
Myoglobin	●	●	●	●	●	●	●	●
N-Acetylprocainamide (NAPA)					●	●		
Nicotine Metabolites							● ²	● ²
Nitrite Validity Test				● ^{3,7,10}				
NT-proBNP	● ²	● ²	● ²		●	●	● ²	● ²
Opiates	●			●	●	●		
Osteocalcin							● ²	● ²
Oxidant Validity Test				● ^{3,7,10}				
Pancreatic Amylase	●			●	● ^{2,6}	● ^{2,6}		
PAP							●	●
PAPP-A	● ¹	● ¹	● ¹				● ²	● ²
pH Validity Test				● ^{3,7,10}				
Phencyclidine	●			●	●	●		
Phenobarbital	●	●	●	●	●	●	●	●
Phenytoin	●	●	●	●	●	●	●	●
Phosphorus	●			● ⁴	●	●		
PIGF	● ¹	● ¹	● ¹					
PIIINP (ELF™ Test)	● ²	● ²	● ²					
Potassium	●			●	●	●		
Prealbumin	●			●	●	●		
Procainamide					●	●		
Procalcitonin (PCT)	●	● ²	● ²					
Progesterone	●	●	●		●		●	●
Prolactin	●	●	●		●		●	●
Propoxyphene	●			●	● ⁷	● ⁷		

Assay	Atellica Solution	ADVIA Centaur XP/ XPT Systems	ADVIA Centaur CP System	ADVIA Chemistry Systems	Dimension Vista Systems	Dimension EXL Systems	IMMULITE 2000/2000 XPi Systems	IMMULITE 1000 System
PSA	● ²	●	●		●	●	●	●
PSA, 3rd Generation							●	
Pseudocholinesterase					●	●		
Pyrilinks-D							●	●
RBC Folate	●	●	●				●	
Retinol Binding Protein					●			
Rheumatoid Factor (RF)	●			●	●	● ^{2,6}		
Rubella IgG	●	●	●				●	●
Rubella IgM	●	●	●				●	●
Salicylate	●			●	●	●		
Serum HER-2/neu	●	●	●					
sFLT-1	● ¹	● ¹	● ¹					
SHBG	●	●	●				●	●
Sirolimus	● ¹	● ¹	● ¹			● ⁸		
Sodium	●			●	●	●		
Soluble Transferrin Receptor (sTfR)	● ^{1,6}				●			
Specific Gravity Test				● ^{3,7,10}				
Syphilis	●	●	●				●	
T Uptake	●	●	●		●	●	●	●
Tacrolimus	● ¹					● ⁸		
Testosterone	●	●	●		●		●	●
Theophylline	●	●	●	●	●	●	●	●
Thyroglobulin (Tg)	● ¹						●	●
Thyroid Binding Globulin (TBG)							●	●
Thyroid Stimulating Immunoglobulin (TSI)							●	
TIMP-1 (ELF™ Test)	● ²	● ²	● ²					
TNF-α								● ²
Tobramycin	●			●	●	●		
Topiramate				● ⁶	● ⁶	● ⁶		
Total Iron Binding Capacity (TIBC)	●			●	●	●		
Total Protein	●			● ⁴	●	●		
Total Protein (CSF/Urine)	●			●	●	●		
Total T3	●	●	●				●	●
Total T4	●	●	●		●	●	●	●
Toxoplasma IgG	●	●	●				●	●
Toxoplasma IgM	●	●	● ¹				●	●
Transferrin	●			●	●	●		
Tricyclic Antidepressants	● ⁷			●	● ⁷	● ⁷		
Triglycerides	●			● ⁴	●	●		
Troponin							●	●
Troponin I, Guideline Acceptable	● ¹⁵	● ¹⁵	● ¹⁵		●	●		
Troponin I, High-Sensitivity (TNIH)	●	● ²			● ²	● ²		
TSH		●	●				●	●
TSH 3rd Generation					●	●	●	●
TSH3-Ultra	●	●	●					
Unconjugated Estriol (UE3)							●	●
Urea Nitrogen (BUN)	●			● ⁴	●	●		
Uric Acid	●			● ⁴	●	●		
Valproic Acid	●	●	●	●	●	●	●	●
Vancomycin	●	●	●	●	●	●		
Vitamin B12	●	●	●		●	●	●	●
Vitamin D Total	●	●	● ¹		●	●		
Zika Test	● ¹⁴	● ¹⁴	● ¹					
Zonisamide				● ⁶	● ⁶	● ⁶		

3gAllergy, ADVIA, ADVIA Centaur, Atellica, CardioPhase, Dimension, Dimension Vista, ELF, EMIT, EXL, IMMULITE, LOCI, Syva, and all associated marks are trademarks of Siemens Healthcare Diagnostics Inc., or its affiliates. All other trademarks and brands are the property of their respective owners.

Product availability may vary from country to country and is subject to varying regulatory requirements. Please contact your local representative for availability.

References:

1. Under development. Not commercially available.
Future availability cannot be guaranteed.
2. Not available for sale in the U.S.
3. For forensic toxicology use only
4. Also available in concentrated version
5. Only available in concentrated version
6. Alliance Application manufactured by third party, distributed by Siemens Healthcare Diagnostics.
7. Alliance Application manufactured and distributed by Siemens Healthcare Diagnostics.
8. No manual pre-treatment
9. Not available for sale in the U.S on the ADVIA Centaur XPT System
10. Not available for sale on the ADVIA Chemistry XPT System.
11. Not CE Marked
12. Available for sale only in Japan
13. Assay developed, manufactured, and sold by Siemens Healthcare Diagnostics Inc. for Ortho Clinical Diagnostics, Inc. and Grifols Diagnostic Solutions Inc.
14. The ADVIA Centaur Zika Test has been authorized by FDA under an EUA for use by authorized laboratories. This test is only authorized for the duration of the declaration that circumstances exist justifying the authorization of the emergency use of in vitro diagnostic tests for detection of Zika virus and/or diagnosis of Zika virus infection under section 564(b)(1) of the Act, 21 U.S.C. § 360bbb-3(b)(1), unless the authorization is terminated or revoked sooner.
15. Tnl-Ultra assay®

Siemens Healthineers Headquarters

Siemens Healthcare GmbH
Henkestr. 127
91052 Erlangen, Germany
Phone: +49 9131 84-0
siemens.com/healthineers

Legal Manufacturer

Siemens Healthcare Diagnostics Inc.
Laboratory Diagnostics
511 Benedict Avenue
Tarrytown, NY 10591-5005
USA
Phone: +1 914-631-8000