



Global Test Menu

IMMULITE Immunoassay Systems

Improve laboratory testing with one of the largest automated immunoassay menus available, from routine and specialty tests to over 400 allergens.

The highly reliable IMMULITE® 2000 XPi system is easy to use and has one of the largest automated immunoassay menus available. Medium- to high-volume laboratories can incorporate specialty and allergy testing into routine workloads to improve productivity and efficiency.

The IMMULITE® 1000 system is a bench-top immunoassay analyzer with an extensive menu and high reliability.

siemens-healthineers.com



IMMULITE 2000/2000 XPi Immunoassay System



IMMULITE 1000 Immunoassay System

IMMULITE Immunoassay Systems

Global Test Menu

▲ IMMULITE 1000

● IMMULITE 2000 and IMMULITE 2000 XPI

Allergy

- ▲* ●* AlaTOP Allergy Screen
 - Allergen-Specific IgE 3gAllergy™
 - * Allergen-Specific IgG
 - * Allergen-Specific IgG4
- ▲* ●* ECP
- ▲ ● IgE, Total

Anemia

- ▲* ●* EPO
- ▲ ● Ferritin
 - Folate
 - RBC Folate
- ▲ ● Vitamin B12

Autoimmune

- Anti-CCP

Bone Metabolism

- ▲* ●* Osteocalcin
- ▲ ● PTHrP

Cardiac

- ▲* ●* CKMB
- ▲* ●* D-Dimer
- ▲ ● High-Sensitivity CRP
- ▲ ● Myoglobin
- ▲* ●* NT-proBNP
- ▲ ● Troponin I

Diabetes

- ▲ ● C-Peptide
- ▲ ● Insulin
- ▲ ● Microalbumin

Growth

- ▲ ● Growth Hormone (hGH)
- ▲ ● IGF-I
- IGFBP-3

Hepatitis

- HBsAb
- HBsAb Quantitative
- HbC IgM
- HbC Total
- HBsAg
- HBsAg Confirmatory

Inflammation

- ▲* IL-1B
- ▲* IL-10
- ▲* ●* IL-2R
- ▲* ●* IL-6
- ▲* IL8
- ▲* ●* LBP
- ▲* TNF-a

Metabolic

- ▲ ● ACTH
- ▲ ● Cortisol
- ▲ ● Homocysteine

Oncology

- ▲ ● AFP
- ▲ ● CA 125 (OM-MA)
- ▲ ● CA 15-3 (BR-MA)
- ▲* ●* CA 19-9 (GI-MA)
- ▲ ● Calcitonin
- ▲ ● CEA
- ▲ ● Free PSA
- ▲ ● PAP
- ▲ ● PSA
- ▲ PSA, 3rd Generation

Reproductive Endocrinology

- ▲ ● Androstenedione
- ▲ ● DHEAS
- ▲ ● Estradiol
- ▲* ●* Free Beta HCG
- ▲ ● FSH
- ▲ ● hCG
- ▲ ● LH
- ▲* ●* PAPP-A
- ▲ ● Progesterone
- ▲ ● Prolactin
- ▲ ● SHBG
- ▲ ● Testosterone
- ▲ ● Unconjugated Estriol

Special ID

- * EBV-EBNA IgG
- * EBV-VCA IgG
- * EBV-VCA IgM
- ▲* ● H. pylori IgG
- Syphilis

Therapeutic Drug Monitoring (TDM)

- ▲ ● Carbamazepine
- ▲* ●* Digitoxin
- ▲ ● Digoxin
- ▲ ● Phenobarbital
- ▲ ● Phenytoin
- ▲ ● Theophylline
- ▲ ● Valproic Acid

Thyroid

- ▲ ● Anti-TG
- ▲ ● Anti-TPO
- ▲ ● Free T3
- ▲ ● Free T4
- ▲ ● Intact PTH
- ▲ ● T Uptake
- ▲ ● Thyroid Binding Globulin (TBG)
- ▲ ● Thyroglobulin (Tg)
- ▲ ● Total T3
- ▲ ● Total T4
- ▲ ● TSH
- ▲ ● TSH, 3rd Generation
 - Thyroid Stimulating Immunoglobulin (TSI)

ToRCH

- ▲ ● CMV IgG
- ▲ ● CMV IgM
- ▲ ● Herpes I & II IgG
- ▲ ● Rubella IgG
- ▲ ● Rubella IgM
- ▲ ● Toxoplasma IgG
- ▲ ● Toxoplasma IgM

Veterinary

- Canine TLI
- ▲ ● Canine Total T4
- ▲ ● Canine TSH
- ▲ ● Canine FT4

Other

- ▲ ● β -2 Microglobulin
- ▲ ● Gastrin
- ▲* ●* Nicotine Metabolites

*Not available for sale in the U.S.

3gAllergy, IMMULITE, and all associated marks are trademarks of Siemens Healthcare Diagnostics Inc., or its affiliates. All other trademarks and brands are the property of their respective owners.

Product availability may vary from country to country and is subject to varying regulatory requirements. Please contact your local representative for availability.

Siemens Healthineers Headquarters

Siemens Healthcare GmbH
Henkestr. 127
91052 Erlangen, Germany
Phone: +49 9131 84-0
siemens-healthineers.com

Published by

Siemens Healthcare Diagnostics Inc.
Laboratory Diagnostics
511 Benedict Avenue
Tarrytown, NY 10591-5005
USA
Phone: +1 914-631-8000