

Chemistry and Immunoassay Menu

For use
in the
U.S. only

siemens-healthineers.us



Assay	Atellica® Solution	ADVIA Centaur® XP/XPT Systems	ADVIA Centaur® CP System	ADVIA® Chemistry Systems	Dimension Vista® System	Dimension® EXL™/ LM/200 Systems	IMMULITE® 2000/2000 XPi Systems
6-Acetylmorphine (6-AM)	● ⁷			● ⁷	● ⁷	● ⁷	
α1-Acid Glycoprotein	●			●	●		
α1-Antitrypsin (AAT)	●			●	●		
α1-Microglobulin					●		
α2-Macroglobulin					●		
Acetaminophen	●			●	●	●	
Acid Phosphatase						●	
ACTH	● ¹						●
Active-B12	●	●	●				
AFP	●	●	●		●		●
Alanine Aminotransferase (ALT)	●			● ⁴			
Alanine Aminotransferase (P5P)	●			● ⁴	●	●	
Albumin (BCG)	●			● ⁴			
Albumin (BCP)	●			●	●	●	
Albumin, Nephelometry					●		
Alkaline Phosphatase	●			● ⁵	●	●	
Allergen-Specific IgE 3gAllergy™							●
AMH (Anti-Müllerian Hormone)	● ¹	● ¹	● ¹				
Amikacin	● ⁷				● ⁷	● ⁷	
Ammonia	●			●	●	●	
Amphetamines	●			●	●	●	
Amylase	●			●	●	●	
Androstenedione	● ¹	● ¹	● ¹				●
Anti-CCP	●	●	●				●
Antistreptolysin O (ASO)	●			●	●		
Anti-TG	●	●	●				●
Anti-TPO	●	●	●				●

Assay	Atellica Solution	ADVIA Centaur XP/XPT Systems	ADVIA Centaur CP System	ADVIA Chemistry Systems	Dimension Vista System	Dimension EXL/LM/200 Systems	IMMULITE 2000/2000 XPi Systems
Apolipoprotein A-I	●			●	●		
Apolipoprotein B	●			●	●		
Aspartate Aminotransferase (AST)	●			● ⁴			
Aspartate Aminotransferase (P5P)	●			● ⁴	●	●	
β-2 Microglobulin	●			●	●		●
Barbiturates, Serum	● ⁷			●	● ⁷	● ⁷	
Barbiturates, Urine	●			●	●	●	
Benzodiazepines, Serum	● ⁷			●	● ⁷	● ⁷	
Benzodiazepines, Urine	●			●	●	●	
Bilirubin, Direct	●			●	●	●	
Bilirubin, Total	●			●	●	●	
BNP	●	●	●				
BR 27.29	●	●					
Buprenorphine	● ⁷			● ⁷	● ⁷	● ⁷	
C-Peptide	●	●	●				●
C1 Inhibitor					●		
CA 125II™ (OM-MA) ²	●	●	●		●		●
CA 15-3 (BR-MA) ²	●	●	●		●		●
CA 19-9 (GI-MA) ²	●	●	●		●		
Caffeine	● ⁷				● ⁷	● ⁷	
Calcitonin	●	●	● ¹				●
Calcium (Arsenazo)	●			● ⁴			
Calcium (CPC)	●			● ⁴	●	●	
Canine Free T4							●
Canine TLI							●
Canine Total T4							●
Canine TSH							●
Cannabinoids (THC)	●			●	●	●	
Carbamazepine	●	●	●	●	●	●	●
Carbon Dioxide, Enzymatic	●			● ⁵	●	●	
CEA	●	●	●		●		●
Ceruloplasmin	● ⁶				●		
Chloride	●			●	●	●	
Cholesterol	●			● ⁴	●	●	
Cholinesterase	●			●	●	●	
CKMB	●	●	●		●	●	
CKMB Activity					●	●	
CMV IgG	●	●	●				●
CMV IgM	● ¹	● ¹	● ¹				●
Cocaine Metabolite	●			●	●	●	

Assay	Atellica Solution	ADVIA Centaur XP/XPT Systems	ADVIA Centaur CP System	ADVIA Chemistry Systems	Dimension Vista System	Dimension EXL/LM/200 Systems	IMMULITE 2000/2000 XPi Systems
Complement C3	●			●	●	●	
Complement C4	●			●	●	●	
Complexed PSA	●	●	●				
Cortisol	●	●	●				●
Creatine Kinase	●			●	●	●	
Creatinine	●			● ⁴	●	●	
Creatinine, Enzymatic	●			●	●	●	
Creatinine Validity Test	● ^{3,7}						
CRP	●			●	●	●	
CRP, High Sensitivity	●			●	●	●	●
CRP, Wide Range				●		●	
Cyclosporine	●	●	●		● ⁹	● ⁹	
Cyclosporine, Extended Range					● ⁹	● ⁹	
Cystatin C	●			●	●		
DHEAS	●	●	●				●
Digitoxin	●	●	●		●	●	
Digoxin	●	●	●	●	●	●	●
EBV-EBNA IgG	● ¹	● ¹	● ¹				
EBV-VCA IgG	● ¹	● ¹	● ¹				
EBV-VCA IgM	● ¹	● ¹	● ¹				
Ecstasy	●			●	●	●	
Enhanced Estradiol	●	●	●				
Enhanced Liver Fibrosis (ELF™) Test	● ¹	● ¹	● ¹				
EPO	● ¹	●	● ¹				
Estradiol					●		●
Ethosuximide					● ⁷	● ⁷	
Ethyl Alcohol	●			●	●	●	
Ethyl Glucuronide (EtG)	● ^{3,6}						
Everolimus	● ¹	● ¹	● ¹			● ¹	
Fentanyl	● ⁶				● ⁶	● ⁶	
Ferritin	●	●	●	●	●	●	●
Folate	●	●	●		●	●	●
Free βHCG ⁸	● ⁸	● ⁸	● ⁸				
Free Light Chains, Type Kappa	● ⁷						
Free Light Chains, Type Lambda	● ⁷						
Free PSA	● ¹	● ¹	● ¹		●	●	●
Free T3	●	●	●		●	●	●
Free T4	●	●	●		●	●	●
Fructosamine	●			●			
FSH	●	●	●		●		●

Assay	Atellica Solution	ADVIA Centaur XP/XPT Systems	ADVIA Centaur CP System	ADVIA Chemistry Systems	Dimension Vista System	Dimension EXL/LM/200 Systems	IMMULITE 2000/2000 XPi Systems
Gamma Glutamyltransferase (GGT)	●			●	●	●	
Gastrin							●
Gentamicin	●	●	●	●	●	●	
Glucose, Hexokinase	●			● ⁴	●	●	
Glucose, Oxidase	●			● ⁴			
Growth Hormone (hGH)	● ¹	● ¹	● ¹				●
<i>H. pylori</i> IgG							●
HA (ELF™ Test)	● ¹	● ¹	● ¹				
Haptoglobin	●			●	●		
HAV IgM	●	●	●				
HAV Total	●	●	●				
HBc IgM	●	●	●				●
HBc Total	●	●	●				●
HBe Ab	● ¹	● ¹	● ¹				
HBeAg	●	●					
HBsAb	●	●	●				●
HBsAg			●				●
HBsAg Confirmatory	●	●	●				●
HBsAg II	●	●					
HBsAg II Quantitative	● ⁸	● ⁸	● ⁸				
hCG	●	●	●		●	●	●
HCV	●	●	●				
HDL Cholesterol	●			●	●	●	
Hemoglobin A1c	● ⁹			● ⁹	● ⁹	● ⁹	
Hemopexin					●		
Herpes I and II IgG							●
Herpes-1 IgG	● ¹	●	●				
Herpes-2 IgG	● ¹	●	●				
HIV 1/O/2 Enhanced (EHIV)			● ¹⁰				
HIV Ag/Ab Combo (CHIV)	● ¹⁰	● ¹⁰					
Homocysteine	●	●	●		●		●
IgE, Total	●	●	●		●		●
IGF-I	● ¹	● ¹	● ¹				●
IGFBP-3	● ¹	● ¹	● ¹				●
IgG Subclasses 1–4					●		
IL-6	● ¹	● ¹	● ¹				● ⁸
Immunoglobulin A (IgA)	●			●	●	●	
Immunoglobulin E (IgE)	●				●		
Immunoglobulin G (IgG)	●			●	●	●	
Immunoglobulin M (IgM)	●			●	●	●	

Assay	Atellica Solution	ADVIA Centaur XP/XPT Systems	ADVIA Centaur CP System	ADVIA Chemistry Systems	Dimension Vista System	Dimension EXL/LM/200 Systems	IMMULITE 2000/2000 XPi Systems
Insulin	●	●	●				●
Intact PTH	●	●	●				●
Iron	●			●	●	●	
Lactate	●			●	●	●	
Lactate Dehydrogenase (L-P)	●			●	●	●	
Lactate Dehydrogenase (P-L)				●			
LBP	● ¹	● ¹	● ¹				
LDL Cholesterol	●			●	●	●	
Levetiracetam	● ^{1,6}						
LH	●	●	●		●		●
Lidocaine	●				●	●	
Lipase	●			●	●	●	
Lipoprotein(a)	●			●			
Lithium	●			●	●	●	
Lysergic Acid Diethylamide (LSD)	● ⁷						
Magnesium	●			● ⁴	●	●	
Methadone	●			●	●	●	
Methadone Metabolites (EDDP)	●			●			
Methaqualone	● ⁷				● ⁷	● ⁷	
Methotrexate	● ⁶			● ⁶	● ⁶	● ⁷	
Microalbumin	●			●	●	●	●
Mycophenolic Acid (MPA)						●	
Myoglobin	●	●	●	●	●	●	●
N-Acetylprocainamide (NAPA)	●				●	●	
Nitrite Validity Test ³	● ⁷						
NT-proBNP	● ¹	● ¹	● ¹		●	●	
Opiates	●			●	●	●	
Oxidant Validity Test ³	● ⁷						
Oxycodone	●			● ⁷	● ⁷	● ⁷	
Pancreatic Amylase	●			●			
PAP							●
PAPP-A	● ⁸	● ⁸	● ⁸				
pH Validity Test ³	● ⁷						
Phencyclidine	●			●	●	●	
Phenobarbital	●	●	●	●	●	●	●
Phenytoin	●	●	●	●	●	●	●
Phosphorus	●			● ⁴	●	●	
PIGF	● ¹	● ¹	● ¹				
PIIINP (ELF™ Test)	● ¹	● ¹	● ¹				
Potassium	●			●	●	●	

Assay	Atellica Solution	ADVIA Centaur XP/XPT Systems	ADVIA Centaur CP System	ADVIA Chemistry Systems	Dimension Vista System	Dimension EXL/LM/200 Systems	IMMULITE 2000/2000 XPi Systems
Prealbumin	●			●	●	●	
Procainamide	●				●	●	
Procalcitonin (PCT)	●					● ¹	
Progesterone	●	●	●		●		●
Prolactin	●	●	●		●		●
Propoxyphene	●			●	● ⁷	● ⁷	
PSA	●	●	●		●	●	●
Pyrilinks®-D							●
RBC Folate	●	●	●				●
Retinol Binding Protein					●		
Rheumatoid Factor (RF)	●			●	●		
Rubella IgG	●	●	●				●
Rubella IgM	●	●	●				●
Salicylate	●			●	●	●	
Serum HER-2/neu	●	●	●				
sFLT-1	● ¹	● ¹	● ¹				
SHBG	●	●	●				●
Sirolimus	● ¹	● ¹	● ¹			● ⁹	
Sodium	●			●	●	●	
Soluble Transferrin Receptor (sTfR)					●		
Specific Gravity Validity Test ³	● ⁷						
Syphilis	●	●	●				●
T Uptake	●	●	●		●	●	●
Tacrolimus	●					● ⁹	
Testosterone II	●	●	●		●		●
Theophylline	●	●	●	●	●	●	●
Thyroglobulin (Tg)	● ¹						●
Thyroid Binding Globulin (TBG)							●
Thyroid Stimulating Immunoglobulin (TSI)							●
TIMP-1 (ELF™ Test)	● ¹	● ¹	● ¹				
Tobramycin	●			●	●	●	
Total Iron Binding Capacity (TIBC)	●			●	●	●	
Total Light Chains, Type Kappa					●		
Total Light Chains, Type Lambda					●		
Total Protein	●			● ⁴	●	●	
Total Protein (CSF/Urine)	●			●	●	●	
Total T3	●	●	●				●
Total T4	●	●	●		●	●	●
Toxoplasma IgG	●	●	●				●
Toxoplasma IgM	●	●	●				●

Assay	Atellica Solution	ADVIA Centaur XP/XPT Systems	ADVIA Centaur CP System	ADVIA Chemistry Systems	Dimension Vista System	Dimension EXL/LM/200 Systems	IMMULITE 2000/2000 XPi Systems
Transferrin	●			●	●	●	
Tricyclic Antidepressants	● ⁷			●	● ⁷	● ⁷	
Triglycerides	●			● ⁴	●	●	
Troponin I, Guideline Acceptable			●		●	●	
Troponin I, High-Sensitivity (TNIH)	●	●	● ¹		●	●	
TSH		●	●				●
TSH 3rd Generation					●	●	●
TSH3-Ultra	●	●	●				
Unconjugated Estriol (UE3)							●
Urea Nitrogen (BUN)	●			● ⁴	●	●	
Uric Acid	●			● ⁴	●	●	
Valproic Acid	●	●	●	●	●	●	●
Vancomycin	●	●	●	●	●	●	
Vitamin B12	●	●	●		●	●	●
Vitamin D Total	●	●				●	
Zika Test	● ¹	●	●				

References

1. Under development. Not commercially available. Future availability cannot be guaranteed.
2. CA 125II, CA 15-3, and CA 19-9 are trademarks of Fujirebio Diagnostics, Inc.
3. For forensic toxicology use only.
4. Also available in concentrated version.
5. Only available in concentrated version.
6. Alliance Application manufactured by third party, distributed by Siemens Healthcare Diagnostics.
7. Alliance Application manufactured and distributed by Siemens Healthcare Diagnostics.
8. For research use only in the U.S.
9. No manual pre-treatment.
10. Assays are developed, manufactured and sold by Siemens for Ortho-Clinical Diagnostics and Grifols Diagnostic Solutions.

At Siemens Healthineers, our purpose is to enable healthcare providers to increase value by empowering them on their journey toward expanding precision medicine, transforming care delivery, and improving patient experience, all made possible by digitalizing healthcare.

An estimated 5 million patients globally benefit every day from our innovative technologies and services in the areas of diagnostic and therapeutic imaging, laboratory diagnostics, and molecular medicine, as well as digital health and enterprise services.

We are a leading medical technology company with over 120 years of experience and 18,000 patents globally. Through the dedication of more than 50,000 colleagues in 75 countries, we will continue to innovate and shape the future of healthcare.

3gAllergy, ADVIA, ADVIA Centaur, Atellica, CardioPhase, Dimension, Dimension Vista, ELF, EMIT, EXL, IMMULITE, LOCI, Syva, and all associated marks are trademarks of Siemens Healthcare Diagnostics Inc., or its affiliates. All other trademarks and brands are the property of their respective owners.

Product availability may vary from country to country and is subject to varying regulatory requirements. Please contact your local representative for availability.

Siemens Healthineers Headquarters

Siemens Healthcare GmbH
Henkestr. 127
91052 Erlangen, Germany
Phone: +49 9131 84-0
siemens-healthineers.com

Local Contact Information

Siemens Healthcare Diagnostics Inc.
Laboratory Diagnostics
511 Benedict Avenue
Tarrytown, NY 10591-5005
USA
Phone: +1 914-631-8000