



Test Menu

Atellica Solution

For use
in the
U.S.



Flexible, scalable, automation-ready immunoassay and clinical chemistry analyzers engineered to deliver control and simplicity so you can drive better outcomes

Experience the power of the Atellica® Solution, featuring patented bidirectional magnetic sample transport technology, the flexibility to create over 300 customizable configurations, and a broad assay menu with proven detection technologies.



Chemistry

Diabetes

Fructosamine
Hemoglobin A1c (Enzymatic)

Drugs of Abuse/Toxicology

6-Acetylmorphine (6-AM)*
Acetaminophen
Amphetamines
Barbiturates, Urine
Barbiturates, Serum*
Benzodiazepines, Urine
Benzodiazepines, Serum*
Buprenorphine*
Cannabinoids (THC)
Cocaine Metabolite
Ecstasy
Ethyl Alcohol
Fentanyl††
Lysergic Acid Diethylamide (LSD)*
Methadone
Methadone Metabolite (EDDP)
Methaqualone*
Opiates
Oxycodone
Phencyclidine
Propoxyphene
Salicylate
Tricyclic Antidepressants*

General Chemistry

Alanine Aminotransferase (ALT)
Alanine Aminotransferase (P5P)
Albumin (BCG)
Albumin (BCP)
Alkaline Phosphatase
Ammonia
Amylase
Aspartate Aminotransferase (AST)
Aspartate Aminotransferase (P5P)
Bilirubin, Direct
Bilirubin, Total
Calcium (Arsenazo)
Calcium (CPC)
Carbon Dioxide
Chloride
Cholesterol
Cholinesterase
Creatine Kinase
Creatinine
Creatinine (Enzymatic)
Gamma-Glutamyl Transferase (GGT)
Glucose (Hexokinase)
Glucose (Oxidase)
HDL Cholesterol
Iron
Lactate
Lactate Dehydrogenase (L-P)
LDL Cholesterol
Lipase
Magnesium
Microalbumin

Pancreatic Amylase
Phosphorus
Potassium
Sodium
Total Iron Binding Capacity (TIBC)
Total Protein
Total Protein, Urine
Triglycerides
Urea Nitrogen (BUN)
Uric Acid

Immunosuppressant Drugs

Tacrolimus

Specific Proteins

α1-Acid Glycoprotein (AAG)
α1-Antitrypsin (AAT)
Antistreptolysin O (ASO)
Apolipoprotein A-1
Apolipoprotein B
β-2 Microglobulin
Ceruloplasmin†
Complement C3
Complement C4
CRP
CRP, High Sensitivity
Cystatin C
Free Light Chain kappa*
Free Light Chain lambda*
Haptoglobin
Immunoglobulin A (IgA)
Immunoglobulin G (IgG)
Immunoglobulin M (IgM)
Lipoprotein(a)
Prealbumin
Rheumatoid Factor (RF)
Transferrin

Specimen Validity Testing

Creatinine*
Nitrite*
Oxidant*
pH*
Specific Gravity*

Therapeutic Drug Monitoring

Amikacin*
Caffeine*
Carbamazepine
Digoxin
Gentamicin
Levetiracetam††
Lidocaine
Lithium
Methotrexate†
N-Acetylprocainamide (NAPA)
Phenobarbital
Phenytoin
Procainamide
Theophylline
Tobramycin
Valproic Acid
Vancomycin

[siemens-healthineers.us/atellicsolution](https://www.siemens-healthineers.us/atellicsolution)

*Alliance application manufactured and distributed by Siemens Healthcare Diagnostics Inc.

†Alliance application manufactured by third party, distributed by Siemens Healthcare Diagnostics Inc.

‡Under development. Not commercially available. Future availability cannot be guaranteed.

Atellica Portfolio of Laboratory Products

Engineered by Siemens Healthineers to deliver control and simplicity so you can drive better outcomes.

Tighter control of your lab, simplified workflow, and more time to focus on driving better business and clinical outcomes—that's the promise of our Atellica® portfolio of laboratory products.

Control. Simplicity. Better Outcomes.

Atellica Solution Test Menu



Immunoassay

Anemia

Active-B12
EPO[‡]
Ferritin
Folate
RBC Folate
Vitamin B12

Autoimmune

Anti-CCP

Bone Metabolism

Intact PTH
Vitamin D Total

Cardiac

BNP
CKMB
High-Sensitivity Troponin I (TnIH)
Myoglobin
NT-proBNP[‡]

Diabetes

C-Peptide
Insulin

Growth

Growth Hormone (hGH)[‡]
IGFBP-3[‡]
IGF-1[‡]

Hepatitis

Anti-HBe[‡]
Anti-HBs 2
HAV IgM
HAV Total
HBc IgM
HBc Total
HBeAg
HBsAg II
HBsAg Confirmatory
HCV

HIV

HIV 1/O/2 Enhanced (EHIV)**
HIV Ag/Ab Combo (CHIV)**

Immunosuppressant Drugs

Cyclosporine
Everolimus[‡]
Sirolimus[‡]

Inflammation

IgE, Total
IL-6[‡]
LBP[‡]

Metabolic

ACTH[‡]
Cortisol
Homocysteine

Oncology

AFP
BR 27.29
CA 125II^{™§}
CA 15-3^{™§}
CA 19-9^{™§}
Calcitonin
CEA
Complexed PSA
Free PSA[‡]
PSA
Serum HER-2/neu

Reproductive Endocrinology

Androstenedione[‡]
Anti-Mullerian Hormone (AMH)[‡]
DHEAS
Enhanced Estradiol
FSH
hCG
LH
PIGF[‡]
Progesterone
Prolactin
sFLT-1[‡]
SHBG
Testosterone II

Sepsis

Procalcitonin (PCT)

Special ID

EBV-EBNA IgG[‡]
EBV-VCA IgG[‡]
EBV-VCA IgM[‡]
Syphilis
Zika Test[‡]

Therapeutic Drug Monitoring

Digitoxin
Digoxin

Thyroid

Anti-TG
Anti-TPO
Free T3
Free T4
Thyroglobulin (Tg)[‡]
Total T3
Total T4
TSH3-Ultra
T Uptake

TORCH

CMV IgG
CMV IgM[‡]
Herpes-1 IgG[‡]
Herpes-2 IgG[‡]
Rubella IgG
Rubella IgM
Toxoplasma IgG
Toxoplasma IgM

For use
in the
U.S.

[‡]Under development. Not commercially available. Future availability cannot be guaranteed.

[§]CA 125II, CA 15-3, and CA 19-9 are trademarks of Fujirebio Diagnostics, Inc.

**Assay developed, manufactured, and sold by Siemens Healthcare Diagnostics Inc. for Ortho Clinical Diagnostics, Inc. and Grifols Diagnostic Solutions Inc.

Atellica and all associated marks are trademarks of Siemens Healthcare Diagnostics Inc., or its affiliates. All other trademarks and brands are the property of their respective owners.

Product availability may vary from country to country and is subject to varying regulatory requirements. Please contact your local representative for availability.

Siemens Healthineers Headquarters

Siemens Healthcare GmbH
Henkestr. 127
91052 Erlangen, Germany
Phone: +49 9131 84-0
siemens-healthineers.com

Published by

Siemens Healthcare Diagnostics Inc.
Laboratory Diagnostics
511 Benedict Avenue
Tarrytown, NY 10591-5005
USA
Phone: +1 914-631-8000