



Cardiology

The complete, portable patient care solution

ACUSON P300 Ultrasound System

Mobile. Powerful. Extraordinarily versatile.

Small in size and big on performance, the ACUSON P300™ ultrasound system is a complete, portable cardiology imaging solution. With excellent image quality and enhanced workflow, the system allows you to evaluate cardiac anatomy and ventricular function. It's a powerful mobile platform capable of easily carry out routine echo exams and more.



Delivering the power to see more.

Powered by a dual-processor, the system is able to keep up with your echo needs. Advanced imaging technologies come standard such as speckle reduction to provide excellent detail and contrast resolution. The system maintains high frame rates and sensitive color Doppler to give you diagnostic confidence.



Providing a fully-featured cardiac solution.

The system supports a complete suite of cardiac transducers that enables flexibility to scan a variety of patient body types. With neonate, pediatric and adult phased array transducers, as low as 3 MHz and up to 11 MHz, you can achieve superb real-time deep or superficial tissue imaging. Additional capabilities include Doppler tissue imaging for myocardial functional evaluation, anatomical M-mode for free angle analysis of left ventricular wall, and stress echo to determine wall motion abnormalities.




Designed to work the way you need it.


The ACUSON P300 system features a small footprint and a mobile cart with hydraulic, adjustable height, making it easy to use, store and move from room to room. Designed with customizable presets, cardiac measurements and reporting, a 15-inch display, integrated power supply, battery that last for 80 minutes, two transducer ports and three USB ports, the ACUSON P300 ultrasound system was designed with you in mind.

For more information, visit
www.siemens.com/ACUSONP300


Answers for life.




Left:
Three chamber view




Right:
Four chamber mitral regurgitation with Color Doppler




Left:
Spectral Doppler
Tissue Imaging



Right:
Two line Anatomical
M-mode



Left:
Stress echo



Right:
Color Doppler
Tissue Imaging

ACUSON P300 is a trademark of Siemens Medical Solutions USA, Inc.

Global Siemens Headquarters
Siemens AG
Wittelsbacherplatz 2
80333 Muenchen

Global Siemens Healthcare Headquarters
Siemens AG
Healthcare Sector
Henkestraße 127
91052 Erlangen
Germany
Phone: +49 9131 84-0

Legal Manufacturer
Siemens Medical Solutions USA, Inc.
Ultrasound
685 E. Middlefield Road
Mountain View, CA 94043
USA
Phone: 1-888-826-9702
www.siemens.com/ultrasound

Order No. A91US-288-1C-4A00 | Printed in Germany | CC US 2116 05141. | © 05.2014, Siemens Medical Solutions USA, Inc.