



Global Test Menu

Dimension Vista 500 and 1500 Intelligent Lab Systems

Speed and quality without compromise.

The Dimension Vista® Intelligent Lab Systems provide intelligent analytics in which sample-centric design, unique integration of four technologies including LOCI® advanced chemiluminescence technology, and customer-driven engineering all come together for a more efficient workflow.

- Incorporate Lean principles with a sample-centric design for simplified, consolidated sample processing.
- Integrate four unique technologies to allow simultaneous processing of tests for multiple disease states on a single platform from a single tube.
- Eliminate many manual tasks with customer-driven engineering, freeing up technical time to address critical issues throughout the lab.



Dimension Vista 500 Intelligent Lab System

siemens-healthineers.com

Dimension Vista 500 and 1500 Intelligent Lab Systems

Global Test Menu

Anemia Ferritin Folate Vitamin B12	General Chemistry (cont.) Alkaline Phosphatase (ALP) Ammonia Amylase Aspartate Aminotransferase Bilirubin, Direct Bilirubin, Total Calcium (CPC) Carbon Dioxide Chloride Cholesterol Creatinine Creatinine (Enzymatic) Creatine Kinase Dibucaine Number ^{††} Gamma Glutamyltransferase (GGT) Glucose Glucose, Hemolyzed [§] HDL Cholesterol Iron Lactate Lactate Dehydrogenase LDL Cholesterol Lipase Magnesium Microalbumin Pancreatic Amylase ^{††} Phosphorus Potassium Pseudocholinesterase Sodium Total Iron Binding Capacity Total Protein Total Protein, CSF/Urine Triglycerides Urea Nitrogen (BUN) Uric Acid	Metabolic Homocysteine	Specific Proteins (cont.) Immunoglobulin M Lipoprotein(a) Ultra ^{††} Prealbumin Retinol Binding Protein Rheumatoid Factor (RF) Soluble Transferrin Receptor (sTfR) Transferrin
Cardiac BNP [*] CKMB Mass CardioPhase [®] hsCRP High-Sensitivity Troponin I Myoglobin NT-proBNP Troponin I	Diabetes Fructosamine ^{††} Hemoglobin A1c [†]	Oncology AFP CA 125II CA 15-3 CA 19-9 CEA Free PSA Total PSA	Therapeutic Drug Monitoring (TDM) Amikacin [§] Caffeine [§] Carbamazepine Digoxin Digoxin Ethosuximide [§] Gentamicin Lidocaine Lithium Methotrexate [†] N-Acetylprocainamide (NAPA) Phenobarbital Phenytoin Procainamide Theophylline Tobramycin Valproic Acid Vancomycin
Drugs of Abuse/Toxicology 6-Acetylmorphine (6-AM) [§] Acetaminophen Amphetamines Barbiturates, Urine Barbiturates, Serum [§] Benzodiazepines, Urine Benzodiazepines, Serum [§] Buprenorphine [§] Cannabinoids (THC) Cocaine Metabolite Ecstasy Ethyl Alcohol Fentanyl [†] Methadone Methaqualone [§] Opiates Oxycodone [§] Phencyclidine Propoxyphene [§] Salicylate Tricyclic Antidepressants [§]	Immunosuppressant Drugs Cyclosporine [†] Cyclosporine, Extended Range [†]	Reproductive Endocrinology Estradiol FSH hCG LH Progesterone Prolactin Testosterone	Specific Proteins α1-Acid Glycoprotein α1-Antitrypsin α1-Microglobulin α2-Macroglobulin β-2 Microglobulin Antistreptolysin O (ASO) Apolipoprotein A-I Apolipoprotein B C1 Inhibitor Ceruloplasmin Complement C3 Complement C4 CRP Cystatin C Haptoglobin Hemopexin Ig Light Chains, Type Kappa Ig Light Chains, Type Lambda IgG Subclass 1 IgG Subclass 2 IgG Subclass 3 IgG Subclass 4 Immunoglobulin A Immunoglobulin E Immunoglobulin G
General Chemistry Alanine Aminotransferase (ALT) Albumin (BCP) Albumin, Nephelometry Aldolase ^{††}	Inflammation Total IgE		Thyroid Free T3 Free T4 T Uptake Total T4 TSH

** Not available for sale in the U.S.
 † Alliance Application manufactured by third party, distributed by Siemens Healthcare Diagnostics.
 ‡ No manual pre-treatment.
 § Alliance Application manufactured and distributed by Siemens Healthcare Diagnostics.*

CardioPhase, Dimension Vista, LOCI, and all associated marks are trademarks of Siemens Healthcare Diagnostics Inc., or its affiliates. All other trademarks and brands are the property of their respective owners.

Product availability may vary from country to country and is subject to varying regulatory requirements. Please contact your local representative for availability.

Siemens Healthineers Headquarters
 Siemens Healthcare GmbH
 Henkestr. 127
 91052 Erlangen, Germany
 Phone: +49 9131 84-0
 siemens-healthineers.com

Published by
 Siemens Healthcare Diagnostics Inc.
 Laboratory Diagnostics
 511 Benedict Avenue
 Tarrytown, NY 10591-5005
 USA
 Phone: +1 914-631-8000