



Global Test Menu

Dimension Xpand Plus/Rxl Max Integrated Chemistry Systems

The first truly integrated chemistry system

Dimension Xpand Plus Integrated Chemistry System

The Dimension® Xpand® Plus Integrated Chemistry System combines chemistry, STAT, and specialty testing in a single, compact, easy-to-use system.

- 47 assays onboard simultaneously for streamlined efficiency
- Large test menu with more than 120 assays to meet over 90% of testing needs on one system
- Innovative Flex® reagent cartridge technology to eliminate manual sample and reagent pretreatment
- 400 tests/hour

Dimension RxL Max Integrated Chemistry System

The Dimension® RxL Max® Integrated Chemistry System improves work processes by providing true integration of chemistry and immunoassay testing in a single unit.

- 91 assays onboard simultaneously for minimized sample splitting and reduced turnaround time
- Sample integrity analysis, such as HIL determination, without compromising throughput and productivity
- More results from one tube on one system, without sample splitting
- Up to 800 tests/hour, including 100 basic metabolite panel (BMP) samples/hour



siemens-healthineers.com

SIEMENS
Healthineers

Dimension Xpand Plus/RxL Max Integrated Chemistry Systems

Global Test Menu

Anemia	General Chemistry	Phosphorus	Immunoglobulin G
Ferritin	Acid Phosphatase	Potassium	Immunoglobulin M
Cardiac	Alanine Aminotransferase (ALT)	Sodium	Kappa Light Chains*†
CKMB Mass	Albumin (BCP)	Total Iron Binding Capacity	Lambda Light Chains*†
CKMB Activity	Aldolase*†	Total Protein	Lipoprotein (a) Ultra*†
CardioPhase® hsCRP	Alkaline Phosphatase	Total Protein (CSF/Urine)	Prealbumin
Myoglobin	Ammonia	Triglycerides	Rheumatoid Factor (RF)*†
NT-proBNP	Amylase	Urea Nitrogen (BUN)	Transferrin
Troponin I	Aspartate Aminotransferase	Uric Acid	Therapeutic Drug Monitoring
Diabetes	Bilirubin, Direct	Immunosuppressant Drugs	Amikacin [§]
Fructosamine*†	Bilirubin, Total	Cyclosporine [‡]	Caffeine [§]
Hemoglobin A1c [‡]	Calcium	Cyclosporine, Extended Range [‡]	Carbamazepine
Drugs of Abuse/Toxicology	Carbon Dioxide, Enzymatic	Everolimus**	Digitoxin
6-Acetylmorphine (6-AM) [§]	Chloride	Mycophenolic Acid	Digoxin
Acetaminophen	Cholesterol	Sirolimus [‡]	Gentamicin
Amphetamines	Cholinesterase	Tacrolimus [‡]	Lamotrigine***††
Barbiturates, Urine	Creatinine	Oncology	Levetiracetam***††
Barbiturates, Serum [§]	Creatinine, Enzymatic	Free PSA	Lidocaine
Benzodiazepines, Urine	Creatine Kinase	Total PSA	Lithium
Benzodiazepines, Serum [§]	Dibucaine Number*†	Reproductive Endocrinology	Methotrexate [§]
Buprenorphine [§] **	Gamma Glutamyltransferase (GGT)	hCG	N-Acetylprocainamide (NAPA)
Cannabinoids (THC)	Glucose	Specific Proteins	Phenobarbital
Cocaine Metabolite	HDL Cholesterol	α1-Acid Glycoprotein*†	Phenytoin
Ecstasy	Hemolyzed Glucose [§]	β-2 Microglobulin Latex*†	Procainamide
Ethyl Alcohol	Iron	Apolipoprotein A-1*†	Theophylline
Fentanyl††	Lactate	Apolipoprotein B*†	Tobramycin
Metadone	Lactate Dehydrogenase (L-P)	Antistreptolysin O (ASO)*†	Valproic Acid
Methaqualone [§]	LDL Cholesterol	Ceruloplasmin*†	Vancomycin
Opiates	Lipase	Complement C3	Thyroid
Oxycodone [§]	Magnesium	Complement C4	Free T4
Phencyclidine	Microalbumin	CRP	Total T4
Propoxyphene [§]	Pancreatic Amylase*†	CRP Extended Range	TSH
Salicylate		Haptoglobin*†	T Uptake
Tricyclic Antidepressants [§]		Immunoglobulin A	

*Not available for sale in the U.S.

†Alliance Application manufactured by third party, distributed by Siemens Healthcare Diagnostics.

‡No manual pretreatment.

§Alliance Application manufactured and distributed by Siemens Healthcare Diagnostics.

**Under development. Not available for sale.

††Manufactured by third party, distributed by Siemens Healthcare Diagnostics.

CardioPhase, Dimension, Flex, RxL Max, Xpand, and all associated marks are trademarks of Siemens Healthcare Diagnostics Inc., or its affiliates. All other trademarks and brands are the property of their respective owners.

Product availability may vary from country to country and is subject to varying regulatory requirements. Please contact your local representative for availability.

Siemens Healthineers Headquarters

Siemens Healthcare GmbH
Henkestr. 127
91052 Erlangen, Germany
Phone: +49 9131 84-0
siemens-healthineers.com

Published by

Siemens Healthcare Diagnostics Inc.
Laboratory Diagnostics
511 Benedict Avenue
Tarrytown, NY 10591-5005
USA
Phone: +1 914-631-8000