

Absolute Dose Values in Computed Tomography

SOMATOM Perspective (32-slice configuration)

Reference values		Switzerland ¹	Germany ²	European Union ³	USA ⁴
Head Routine	CTDI _{vol} [mGy]	65	60	60	75
Thorax Routine	CTDI _{vol} [mGy]	15	10	30	21
Abdomen Routine	CTDI _{vol} [mGy]	15	15	35	25

Default Siemens Protocol		Standard values*	Standard IR values ^{**/**/**}	Put your current values here
Head Routine	CTDI _{vol} [mGy]	52.8	39.6	
Thorax Routine	CTDI _{vol} [mGy]	8.07	5.65	
Abdomen Routine	CTDI _{vol} [mGy]	12.58	10.38	

1 Bundesamt für Gesundheit (Merkblatt R-06-06, Diagnostische Referenzwerte in der Computertomographie, 01.04.2010).

2 Bundesamt für Strahlenschutz (Diagnostische Referenzwerte für diagnostische und interventionelle Röntgenanwendungen vom 22. Juni 2016).

3 European Guidelines on Quality Criteria for Computed Tomography (<http://www.dr.dk/guidelines/ct/quality/htmlindex.htm>).

4 American College of Radiology (CT Accreditation Program Requirements, Clinical Image Quality Guide, Amended 2014).

*Values are based on the default protocols of the SOMATOM Perspective Family with syngo CT VC40 version and an average sized patient of 1.75 m and 75 kg

**Iterative Reconstruction SAFIRE is used

***In clinical practice, the use of SAFIRE may reduce CT patient dose depending on the clinical task, patient size, anatomical location, and clinical practice. A consultation with a radiologist and a physicist should be made to determine the appropriate dose to obtain diagnostic image quality for the particular clinical task. The following test method was used to determine a 54 to 60% dose reduction when using the SAFIRE reconstruction software. Noise, CT numbers, homogeneity, low-contrast resolution and high contrast resolution were assessed in a Gammex 438 phantom. Low dose data reconstructed with SAFIRE showed the same image quality compared to full dose data based on this test. Data on file.

On account of certain regional limitations of sales rights and service availability, we cannot guarantee that all products included in this brochure are available through the Siemens sales organization worldwide. Availability and packaging may vary by country and is subject to change without prior notice. Some/All of the features and products described herein may not be available in the United States.

The information in this document contains general technical descriptions of specifications and options as well as standard and optional features which do not always have to be present in individual cases.

Siemens reserves the right to modify the design, packaging, specifications and options described herein without prior notice. Please contact your local Siemens sales representative for the most current information.

Note: Any technical data contained in this document may vary within defined tolerances.

International version. Not for distribution in the US.

Siemens Healthineers Headquarters

Siemens Healthcare GmbH
Henkestr. 127
91052 Erlangen
Germany
Phone: +49 9131 84 0
siemens.com/healthineers