

# Absolute Dose Values in Computed Tomography

## SOMATOM go.Now

References values		Switzerland <sup>1</sup>	Germany <sup>2</sup>	European Union <sup>3</sup>	USA <sup>4</sup>
Head Routine	CTDIvol [mGy]	65	60	60	75
Thorax Routine	CTDIvol [mGy]	15	10	30	N/A
Abdomen Routine	CTDIvol [mGy]	15	15	35	25

<sup>1</sup> Bundesamt für Gesundheit (Merkblatt R-06-06, Diagnostische Referenzwerte in der Computertomographie, 01.04.2010, (REV.01.01.2018).

<sup>2</sup> Bundesamt für Strahlenschutz (Diagnostische Referenzwerte für diagnostische und interventionelle Röntgenanwendungen vom 22.06.2016).

<sup>3</sup> European Guidelines on Quality Criteria for Computed Tomography (<http://www.dr.dk/guidelines/ct/quality/htmlindex.htm>).

<sup>4</sup> American College of Radiology (CT Accreditation Program Requirements, Amended 2018).

Default Siemens Protocol	Standard CTDIvol / [mGy]*	Put your current values here
Head Routine	49.53	
Thorax Routine	6.84	
Lung Low Dose with Tin Filter	1.11	
Abdomen Routine	12.44	

\*Values are based on the default protocols of the SOMATOM go.Now with syngo CT VA20A and an average sized patient of 1.75 m and 75 kg.

Iterative Reconstruction SAFIRE is used.

In clinical practice, the use of SAFIRE may reduce CT patient dose depending on the clinical task, patient size, anatomical location, and clinical practice. A consultation with a radiologist and a physicist should be made to determine the appropriate dose to obtain diagnostic image quality for the particular clinical task.

On account of certain regional limitations of sales rights and service availability, we cannot guarantee that all products included in this brochure are available through the sales organization of Siemens Healthineers worldwide.

Availability and packaging may vary by country and is subject to change without prior notice.

Some/All of the features and products described herein may not be available in the United States.

The information in this document contains general technical descriptions of specifications and options as well as standard and optional features which do not always have to be present in individual cases.

The statements by customers of Siemens Healthineers described herein are based on results that were achieved in the customer's unique setting. Since there is no "typical" hospital and many variables exist (e.g., hospital size, case mix, level of IT adoption), there can be no guarantee that other customers will achieve the same results.

The customers cited are employed by an institution that might provide Siemens Healthineers product reference services, R&D collaboration or other relationship for compensation pursuant to a written agreement.

Siemens Healthineers reserves the right to modify the design, packaging, specifications, and options described herein without prior notice. Please contact your local Siemens Healthineers sales representative for the most current information.

Note: Any technical data contained in this document may vary within defined tolerances. Original images always lose a certain amount of detail when reproduced.

The products/features and/or service offerings (here mentioned) are not commercially available in all countries and/or for all modalities. If the services are not marketed in countries due to regulatory or other reasons, the service offering cannot be guaranteed. Please contact your local Siemens Healthineers organization for further details.

.....  
**Siemens Healthineers Headquarters**

Siemens Healthcare GmbH

Henkestr. 127

91052 Erlangen, Germany

Phone: +49 9131 84-0

siemens-healthineers.com

.....

*PDF only · © Siemens Healthcare GmbH, 2018*