

SIEMENS



Transducers

ACUSON X300™ Ultrasound System, Premium Edition (PE)

Release 7.0

TABLE OF CONTENTS

TABLE OF CONTENTS	2	VF13-5SP Transducer	8
CH5-2 Transducer	3	VF13-5 Transducer	8
C6-2 Transducer	3	V5Ms Transducer	9
C7F2 Transducer	4	EV9-4 Transducer	9
C8-5 Transducer	4	EV9F4 Transducer	10
P4-2 Transducer	5	EC9-4 Transducer	10
P5-1 Transducer	5	BP9-4 Transducer	11
P8-4 Transducer	6	CW5 Transducer	11
P9-4 Transducer	6	CW2 Transducer	12
VF8-3 Transducer	7	AcuNav 10F	12
VF10-5 Transducer	7	AcuNav 8F	13



CH5-2 Transducer

Frequency Bandwidth:	1.4 – 5.0 MHz
Compatible with:	ACUSON X300™ ultrasound system ACUSON X150™ ultrasound system SONOLINE G60 S™ ultrasound system SONOLINE G40™ ultrasound system
Exam Types:	Abdomen, Early OB, Emergency Medicine, Fetal Echo, OB/GYN, Peripheral Vascular, Renal, Urology, Venous

Design Attributes:

- Wide bandwidth curved array transducer
- Hanafy lens transducer technology
- User-selectable MultiHertz™ multiple frequency imaging
- Ergonomically designed form factor
- Lightweight transducer with flexible cable



C6-2 Transducer

Frequency Bandwidth:	1.8 – 6.0 MHz
Compatible with:	ACUSON X500™ ultrasound system, SONOLINE G60 S ultrasound system, ACUSON CV70™ cardiovascular system,
Exam Types:	Abdomen, Aorta, Early OB, Fetal Echo, OB/GYN, Pediatric Abdomen, Pediatric Echo, Peripheral Vascular, Renal, Venous

Design Attributes:

- Wide bandwidth curved array transducer
- User-selectable MultiHertz imaging
- Ergonomically designed form factor
- Lightweight transducer with flexible cable
- Curved Vector Format



C7F2 Transducer

Frequency Bandwidth:	1.9 – 6.4 MHz
Compatible with:	ACUSON X500 ultrasound system
Exam Types:	Abdomen, Early OB, Fetal Echo, OB/GYN

Design Attributes:

- Wide bandwidth curved array transducer
- User-selectable MultiHertz imaging
- Ergonomically designed form factor
- Lightweight transducer with flexible cable
- Curved Vector Format



C8-5 Transducer

Compatible with:	ACUSON X300 ultrasound system
Exam Types:	Cerebrovascular, Neonatal Head, Pediatric Abdomen, Pediatric Echo

Design Attributes:

- Wide bandwidth micro-curved array transducer
 - User-selectable MultiHertz imaging
 - Ergonomically designed form factor
 - Lightweight transducer with flexible cable
-



P4-2 Transducer

Frequency Bandwidth:	1.3 – 4.4 MHz
Compatible with:	ACUSON X300 ultrasound system ACUSON X150 ultrasound system SONOLINE G40 ultrasound system
Exam Types:	Abdomen, Adult Echo, Emergency Medicine, OB/GYN, Renal, Transcranial

Design Attributes:

- Wide bandwidth phased array transducer
- User-selectable MultiHertz imaging
- Ergonomically designed form factor
- Lightweight transducer with flexible cable



P5-1 Transducer

Frequency Bandwidth:	1.4 – 5.6 MHz
Exam Types:	Abdomen, Adult Echo, Emergency Medicine, Pediatric Echo, Transcranial

Design Attributes:

- Wide bandwidth phased array single crystal piezoelectric transducer
- User-selectable MultiHertz imaging
- Ergonomically designed form factor
- Lightweight transducer with flexible cable



P8-4 Transducer

Frequency Bandwidth:	2.7 – 8.0 MHz
Compatible with:	ACUSON X150 ultrasound system SONOLINE G40 ultrasound system
Exam Types:	Abdomen, Neonatal Echo, Neonatal Head, Pediatric Abdomen, Pediatric Echo, Renal

Design Attributes:

- Wide bandwidth phased array transducer
- User-selectable MultiHertz imaging
- Ergonomically designed form factor
- Lightweight transducer with flexible cable



P9-4 Transducer

Frequency Bandwidth:	2.8 – 9.2 MHz
Compatible with:	ACUSON X300 ultrasound system ACUSON X500 ultrasound system ACUSON CV70 cardiovascular system SONOLINE G60 S ultrasound system
Exam Types:	Neonatal Echo, Neonatal Head, Pediatric Abdomen, Pediatric Echo

Design Attributes:

- Wide bandwidth phased array transducer
- User-selectable MultiHertz imaging
- Ergonomically designed form factor
- Lightweight transducer with flexible cable



VF8-3 Transducer

Frequency Bandwidth:	2.5 – 10.0 MHz
Compatible with:	ACUSON X300 ultrasound system
Exam Types:	Breast, Cerebrovascular, Emergency Medicine, Musculoskeletal, Orthopedic, Peripheral Vascular, Testicle, Thyroid, Venous

Design Attributes:

- Wide bandwidth linear transducer
- Virtual format imaging
- User-selectable MultiHertz imaging
- Ergonomically designed form factor
- Lightweight transducer with flexible cable



VF10-5 Transducer

Frequency Bandwidth:	4.0 – 11.4 MHz
Compatible with:	ACUSON X300 ultrasound system ACUSON X150 ultrasound system SONOLINE G40 ultrasound system
Exam Types:	Breast, Cerebrovascular, Emergency Medicine, Musculoskeletal, Orthopedic, Peripheral Vascular, Testicle, Thyroid, Venous

Design Attributes:

- Wide bandwidth linear transducer
- Virtual format imaging
- User-selectable MultiHertz imaging
- Ergonomically designed form factor
- 2D beam steering
- Lightweight transducer with flexible cable



VF13-5SP Transducer

Frequency Bandwidth:	4.3 – 13.0 MHz
Compatible with:	ACUSON X300 ultrasound system ACUSON X500 ultrasound system ACUSON CV70 cardiovascular system SONOLINE G60 S ultrasound system SONOLINE G50™ ultrasound system SONOLINE Elegra™ ultrasound system
Exam Types:	Breast, Cerebrovascular, Intraoperative, Musculoskeletal, Superficial Musculoskeletal, Superficial Vascular, Testicle, Thyroid, Venous

Design Attributes:

- Wide bandwidth linear transducer
- Virtual format imaging
- User-selectable MultiHertz imaging
- Ergonomically designed form factor
- Lightweight transducer with flexible cable



VF13-5 Transducer

Frequency Bandwidth:	4.4 – 13.0 MHz
Compatible with:	ACUSON X300 ultrasound system ACUSON X150 ultrasound system SONOLINE G40 ultrasound system
Exam Types:	Breast, Cerebrovascular, Digital, Emergency Medicine, Musculoskeletal, Superficial Musculoskeletal, Penile, Superficial Vascular, Testicle, Thyroid, Venous

Design Attributes:

- Wide bandwidth linear transducer
- Virtual format imaging
- User-selectable MultiHertz imaging
- Ergonomically designed form factor
- Lightweight transducer with flexible cable



V5Ms Transducer

Frequency Bandwidth:	2.7 – 9.0 MHz
Compatible with:	ACUSON S2000™ ultrasound system ACUSON Sequoia™ ultrasound system ACUSON CV70 cardiovascular system ACUSON Cypress™ cardiovascular system ACUSON Aspen™ ultrasound system ACUSON 128XP/10C™ echocardiography system
Exam Types:	Transesophageal Echo

Design Attributes:

- Wide bandwidth transesophageal transducer
- Endoscope diameter = 10.5 mm, length = 11.0 mm
- Adult tip size: width = 14.5 mm, height = 11.5 mm
- Ergonomic design featuring one-hand control with variable speed rotation – 90° per sec.
- RF shielding
- User-selectable MultiHertz imaging



EV9-4 Transducer

Frequency Bandwidth:	2.9 – 9.7 MHz
Compatible with:	ACUSON X300 ultrasound system ACUSON X150 ultrasound system SONOLINE G40 ultrasound system
Exam Types:	Early OB, Emergency Medicine, OB/GYN

Design Attributes:

- Wide bandwidth endovaginal transducer
- User-selectable MultiHertz imaging
- Lightweight transducer with flexible cable



EV9F4 Transducer

Frequency Bandwidth:	2.9 – 9.0 MHz
----------------------	---------------

Exam Types:	Early OB, OB/GYN
-------------	------------------

Design Attributes:

- Wide bandwidth endovaginal volume transducer
- User-selectable MultiHertz imaging
- Lightweight transducer with flexible cable
- Curved Vector Format



EC9-4 Transducer

Frequency Bandwidth:	2.9 – 9.8 MHz
----------------------	---------------

Compatible with:	ACUSON X300 ultrasound system ACUSON X150 ultrasound system SONOLINE G40 ultrasound system
------------------	--

Exam Types:	Early OB, OB/GYN, Urology
-------------	---------------------------

Design Attributes:

- User-selectable MultiHertz imaging
- Ergonomically designed form factor
- Lightweight transducer with flexible cable



BP9-4 Transducer

Frequency Bandwidth: 2.9 – 9.0 MHz

Exam Types: Prostate, Urology

Design Attributes:

- Wide bandwidth curved array transducer
- User-selectable MultiHertz imaging
- Ergonomically designed form factor
- Lightweight transducer with flexible cable
- Live Bi-Plane imaging and biopsy



CW5 Transducer

Selectable CW Doppler Frequencies: 5.0 MHz

Compatible with: ACUSON X300 ultrasound system
ACUSON X500 ultrasound system
SONOLINE G60 S ultrasound system

Exam Types: Cerebrovascular, Pediatric Echo



CW2 Transducer

Selectable CW Doppler Frequencies: 2.0 MHz

Compatible with: ACUSON X300 ultrasound system
ACUSON X500 ultrasound system
SONOLINE G60 S ultrasound system

Exam Types: Adult Echo, Pediatric Echo



AcuNav 10F*

Frequency Bandwidth: 2.2 – 11.0 MHz

Compatible With: ACUSON Sequoia echocardiography system
ACUSON Cypress cardiovascular system
ACUSON Aspen ultrasound system
ACUSON Sequoia ultrasound system

Exam Types: Intracardiac Echo

Design Attributes:

- 10 french catheter (3.3 mm diameter)
- 90 cm insertable length
- Sterile, single-use advanced miniaturization AcuNav™ ultrasound catheter family
- Reusable SwiftLink™ catheter connector
- Four-way steering in two planes: 160° in each direction
- Longitudinal side-fire imaging

* For purchase or inquiries, contact Biosense Webster: USA (1-909-839-8500 and 1-800-729-9010), Belgium (+32-2-352-1411)



AcuNav 8F*

Frequency Bandwidth:	3.0 – 10.0 MHz
-----------------------------	----------------

Compatible With:	ACUSON Sequoia echocardiography system ACUSON CV70 cardiovascular system ACUSON Cypress cardiovascular system ACUSON Sequoia ultrasound system
-------------------------	---

Exam Types:	Intracardiac Echo
--------------------	-------------------

Design Attributes:

- 8 french catheter (2.7 mm diameter)
- 110 cm insertable length
- Sterile, single-use advanced miniaturization AcuNav ultrasound catheter family
- Reusable SwiftLink catheter connector
- Four-way steering in two planes: 160° in each direction
- Longitudinal side-fire imaging

* For purchase or inquiries, contact Biosense Webster: USA (1-909-839-8500 and 1-800-729-9010), Belgium (+32-2-352-1411)

Frequency Bandwidth measurements
represent bandwidth at +/-20dB.

128XP/10C, ACUSON, AcuNav, Aspen,
CV70, Cypress, Elegra, G40, G50, G60 S,
MultiHertz, S2000, Sequoia, SONOLINE,
SwiftLink, X150, X300 and X500 are trade-
marks of Siemens Medical Solutions USA,
Inc.

DS 0311 | © 03.2011, Siemens Medical
Solutions USA, Inc.

Global Siemens Headquarters

Siemens AG
Wittelsbacherplatz 2
80333 Muenchen
Germany

**Global Siemens Healthcare
Headquarters**

Siemens AG
Healthcare Sector
Henkestrasse 127
91052 Erlangen
Telephone: +49 9131 84-0
Germany

www.siemens.com/healthcare

Legal Manufacturer

Siemens Medical Solutions USA, Inc.
Ultrasound
1230 Shorebird Way
Mountain View, CA 94043
USA
Telephone: 1-888-826-9702
www.siemens.com/ultrasound