

SIEMENS



Transducers

ACUSON X300™ Ultrasound System, Premium Edition (PE) - *Women's Imaging*

Release 7.0

TABLE OF CONTENTS

TABLE OF CONTENTS	2
CH5-2 Transducer	3
C6-2 Transducer	3
C7F2 Transducer	4
P4-2 Transducer	4
VF8-3 Transducer	5
VF10-5 Transducer	5
VF13-5SP Transducer	6
VF13-5 Transducer	7
EV9-4 Transducer	7
EV9F4 Transducer	8
EC9-4 Transducer	8



CH5-2 Transducer

Frequency Bandwidth:	1.4 – 5.0 MHz
Compatible with:	ACUSON X300™ ultrasound system ACUSON X150™ ultrasound system SONOLINE G60 S™ ultrasound system SONOLINE G40™ ultrasound system
Exam Types:	Abdomen, Early OB, Emergency Medicine, Fetal Echo, OB/GYN, Peripheral Vascular, Renal, Urology, Venous

Design Attributes:

- Wide bandwidth curved array transducer
- Hanafy lens transducer technology
- User-selectable MultiHertz™ multiple frequency imaging
- Ergonomically designed form factor
- Lightweight transducer with flexible cable



C6-2 Transducer

Frequency Bandwidth:	1.8 – 6.0 MHz
Compatible with:	ACUSON X500™ ultrasound system, SONOLINE G60 S ultrasound system, ACUSON CV70™ cardiovascular system,
Exam Types:	Abdomen, Aorta, Early OB, Fetal Echo, OB/GYN, Pediatric Abdomen, Pediatric Echo, Peripheral Vascular, Renal, Venous

Design Attributes:

- Wide bandwidth curved array transducer
- User-selectable MultiHertz imaging
- Ergonomically designed form factor
- Lightweight transducer with flexible cable
- Curved Vector Format



C7F2 Transducer

Frequency Bandwidth:	1.9 – 6.4 MHz
Compatible with:	ACUSON X500 ultrasound system
Exam Types:	Abdomen, Early OB, Fetal Echo, OB/GYN

Design Attributes:

- Wide bandwidth curved array transducer
- User-selectable MultiHertz imaging
- Ergonomically designed form factor
- Lightweight transducer with flexible cable
- Curved Vector Format



P4-2 Transducer

Frequency Bandwidth:	1.3 – 4.4 MHz
Compatible with:	ACUSON X300 ultrasound system ACUSON X150 ultrasound system SONOLINE G40 ultrasound system
Exam Types:	Abdomen, Adult Echo, Emergency Medicine, OB/GYN, Renal, Transcranial

Design Attributes:

- Wide bandwidth phased array transducer
- User-selectable MultiHertz imaging
- Ergonomically designed form factor
- Lightweight transducer with flexible cable



VF8-3 Transducer

Frequency Bandwidth:	2.5 – 10.0 MHz
Compatible with:	ACUSON X300 ultrasound system
Exam Types:	Breast, Cerebrovascular, Emergency Medicine, Musculoskeletal, Orthopedic, Peripheral Vascular, Testicle, Thyroid, Venous

Design Attributes:

- Wide bandwidth linear transducer
- Virtual format imaging
- User-selectable MultiHertz imaging
- Ergonomically designed form factor
- Lightweight transducer with flexible cable



VF10-5 Transducer

Frequency Bandwidth:	4.0 – 11.4 MHz
Compatible with:	ACUSON X300 ultrasound system ACUSON X150 ultrasound system SONOLINE G40 ultrasound system
Exam Types:	Breast, Cerebrovascular, Emergency Medicine, Musculoskeletal, Orthopedic, Peripheral Vascular, Testicle, Thyroid, Venous

Design Attributes:

- Wide bandwidth linear transducer
- Virtual format imaging
- User-selectable MultiHertz imaging
- Ergonomically designed form factor
- 2D beam steering
- Lightweight transducer with flexible cable



VF13-5SP Transducer

Frequency Bandwidth:	4.3 – 13.0 MHz
Compatible with:	ACUSON X300 ultrasound system ACUSON X500 ultrasound system ACUSON CV70 cardiovascular system SONOLINE G60 S ultrasound system SONOLINE G50™ ultrasound system SONOLINE Elegra™ ultrasound system
Exam Types:	Breast, Cerebrovascular, Intraoperative, Musculoskeletal, Superficial Musculoskeletal, Superficial Vascular, Testicle, Thyroid, Venous

Design Attributes:

- Wide bandwidth linear transducer
- Virtual format imaging
- User-selectable MultiHertz imaging
- Ergonomically designed form factor
- Lightweight transducer with flexible cable



VF13-5 Transducer

Frequency Bandwidth:	4.4 – 13.0 MHz
Compatible with:	ACUSON X300 ultrasound system ACUSON X150 ultrasound system SONOLINE G40 ultrasound system
Exam Types:	Breast, Cerebrovascular, Digital, Emergency Medicine, Musculoskeletal, Superficial Musculoskeletal, Penile, Superficial Vascular, Testicle, Thyroid, Venous

Design Attributes:

- Wide bandwidth linear transducer
- Virtual format imaging
- User-selectable MultiHertz imaging
- Ergonomically designed form factor
- Lightweight transducer with flexible cable



EV9-4 Transducer

Frequency Bandwidth: 2.9 – 9.7 MHz

Compatible with: ACUSON X300 ultrasound system
ACUSON X150 ultrasound system
SONOLINE G40 ultrasound system

Exam Types: Early OB, Emergency Medicine, OB/GYN

Design Attributes:

- Wide bandwidth endovaginal transducer
- User-selectable MultiHertz imaging
- Lightweight transducer with flexible cable



EV9F4 Transducer

Frequency Bandwidth: 2.9 – 9.0 MHz

Exam Types: Early OB, OB/GYN

Design Attributes:

- Wide bandwidth endovaginal volume transducer
- User-selectable MultiHertz imaging
- Lightweight transducer with flexible cable
- Curved Vector Format



EC9-4 Transducer

Frequency Bandwidth:	2.9 – 9.8 MHz
Compatible with:	ACUSON X300 ultrasound system ACUSON X150 ultrasound system SONOLINE G40 ultrasound system
Exam Types:	Early OB, OB/GYN, Urology

Design Attributes:

- User-selectable MultiHertz imaging
- Ergonomically designed form factor
- Lightweight transducer with flexible cable

Frequency Bandwidth measurements
represent bandwidth at +/-20 dB.

128XP/10C, ACUSON, AcuNav, Aspen,
CV70, Cypress, Elegra, G40, G50, G60 S,
MultiHertz, S2000, Sequoia, SONOLINE,
SwiftLink, X150, X300 and X500 are trade-
marks of Siemens Medical Solutions USA,
Inc.

DS 0711 | © 07.2011, Siemens Medical
Solutions USA, Inc.

Global Siemens Headquarters

Siemens AG
Wittelsbacherplatz 2
80333 Muenchen
Germany

**Global Siemens Healthcare
Headquarters**

Siemens AG
Healthcare Sector
Henkestrasse 127
91052 Erlangen
Telephone: +49 9131 84-0
Germany

www.siemens.com/healthcare

Legal Manufacturer

Siemens Medical Solutions USA, Inc.
Ultrasound
1230 Shorebird Way
Mountain View, CA 94043
USA
Telephone: 1-888-826-9702
www.siemens.com/ultrasound