

SIEMENS MAGNETOM TrioTim syngo MR B17

\\USER\20min_protocols\shoulder\shoulder\pd_tse_fs_tra

TA: 2:42 PAT: Off Voxel size: 0.6x0.4x2.0 mm Rel. SNR: 1.00 SIEMENS: tse

Properties

Prio Recon	Off
Before measurement	
After measurement	
Load to viewer	On
Inline movie	Off
Auto store images	On
Load to stamp segments	On
Load images to graphic segments	Off
Auto open inline display	Off
Start measurement without further preparation	On
Wait for user to start	Off
Start measurements	single

Routine

Slice group 1	
Slices	20
Dist. factor	30 %
Position	Isocenter
Orientation	Transversal
Phase enc. dir.	A >> P
Rotation	0.00 deg
Phase oversampling	70 %
FoV read	140 mm
FoV phase	100.0 %
Slice thickness	2.0 mm
TR	4000 ms
TE	31 ms
Averages	1
Concatenations	1
Filter	Normalize, Elliptical filter
Coil elements	SHS

Contrast

MTC	Off
Magn. preparation	None
Flip angle	150 deg
Fat suppr.	Fat sat.
Fat sat. mode	Weak
Water suppr.	None
Restore magn.	On

Averaging mode	Long term
Reconstruction	Magnitude
Measurements	1
Multiple series	Each measurement

Resolution

Base resolution	320
Phase resolution	75 %
Phase partial Fourier	Off
Trajectory	Cartesian
Interpolation	Off

PAT mode	None
Matrix Coil Mode	Auto (CP)

Image Filter	Off
Distortion Corr.	Off
Prescan Normalize	Off
Normalize	On
Intensity	Medium
Cut off	20

Width	4
Unfiltered images	On
B1 filter	Off
Raw filter	Off
Elliptical filter	On
Mode	Inplane

Geometry

Multi-slice mode	Interleaved
Series	Interleaved

Sat. region 1	
Thickness	50 mm
Position	L27.4 A7.4 H12.2
Orientation	S > T-24.0 > C13.9
Special sat.	None

Set-n-Go Protocol	Off
Table position	H
Table position	0 mm
Inline Composing	Off

Tim CT mode	Off

System

Body	Off
SHS	On

Positioning mode	FIX
MSMA	S - C - T
Sagittal	L >> R
Coronal	A >> P
Transversal	H >> F
Coil Combine Mode	Adaptive Combine
AutoAlign	---
Auto Coil Select	Default

Shim mode	Standard
Adjust with body coil	Off
Confirm freq. adjustment	Off
Assume Silicone	Off
? Ref. amplitude 1H	0.000 V
Adjustment Tolerance	Auto
Adjust volume	
Position	Isocenter
Orientation	Transversal
Rotation	0.00 deg
R >> L	140 mm
A >> P	140 mm
F >> H	52 mm

Physio

1st Signal/Mode	None

Dark blood	Off

Resp. control	Off

Inline

Subtract	Off
Std-Dev-Sag	Off
Std-Dev-Cor	Off
Std-Dev-Tra	Off
Std-Dev-Time	Off

SIEMENS MAGNETOM TrioTim syngo MR B17

MIP-Sag	Off
MIP-Cor	Off
MIP-Tra	Off
MIP-Time	Off
Save original images	On

Sequence

Introduction	On
Dimension	2D
Compensate T2 decay	Off
Reduce Motion Sens.	Off
Contrasts	1
Bandwidth	217 Hz/Px
Flow comp.	No
Allowed delay	60 s
Echo spacing	10.5 ms

Define	Turbo factor
Turbo factor	11
Echo trains per slice	38
RF pulse type	Low SAR
Gradient mode	Fast