

SIEMENS MAGNETOM Product syngo MR B17

\\USER\knee\_20min\_0002\20min\_protocols\_NYU\_27.05.09\hip\_4ch\_flex/body\_ok\pd\_tse\_fs\_cor

TA: 4:23 PAT: Off Voxel size: 0.5x0.5x3.0 mm Rel. SNR: 1.00 SIEMENS: tse

Properties

Prio Recon	Off
Before measurement	
After measurement	
Load to viewer	On
Inline movie	Off
Auto store images	On
Load to stamp segments	Off
Load images to graphic segments	Off
Auto open inline display	Off
Start measurement without further preparation	On
Wait for user to start	Off
Start measurements	single

Routine

Slice group 1	
Slices	24
Dist. factor	10 %
Position	Isocenter
Orientation	Coronal
Phase enc. dir.	R >> L
Rotation	0.00 deg
Phase oversampling	65 %
FoV read	150 mm
FoV phase	100.0 %
Slice thickness	3.0 mm
TR	1950 ms
TE	23 ms
Averages	1
Concatenations	1
Filter	Distortion Corr.(2D), Prescan Normalize, Elliptical filter
Coil elements	BO1,2

Contrast

MTC	Off
Magn. preparation	None
Flip angle	150 deg
Fat suppr.	Fat sat.
Fat sat. mode	Strong
Water suppr.	None
Restore magn.	On
-----	
Averaging mode	Long term
Reconstruction	Magnitude
Measurements	1
Multiple series	Each measurement

Resolution

Base resolution	320
Phase resolution	100 %
Phase partial Fourier	Off
Trajectory	Cartesian
Interpolation	Off
-----	
PAT mode	None
Matrix Coil Mode	Auto (CP)
-----	
Image Filter	Off
Distortion Corr.	On
Mode	2D
Unfiltered images	Off
Unfiltered images	Off

Prescan Normalize	On
Normalize	Off
B1 filter	Off
Raw filter	Off
Elliptical filter	On
Mode	Inplane

Geometry

Multi-slice mode	Interleaved
Series	Interleaved
-----	
Special sat.	None
-----	
Set-n-Go Protocol	Off
Table position	H
Table position	0 mm
Inline Composing	Off
-----	
Tim CT mode	Off

System

Body	Off
BO1	On
BO2	On
-----	
Positioning mode	ISO
MSMA	S - C - T
Sagittal	R >> L
Coronal	A >> P
Transversal	H >> F
Coil Combine Mode	Adaptive Combine
AutoAlign	---
Auto Coil Select	Default
-----	
Shim mode	Standard
Adjust with body coil	Off
Confirm freq. adjustment	Off
Assume Silicone	Off
? Ref. amplitude 1H	0.000 V
Adjustment Tolerance	Auto
Adjust volume	
Position	Isocenter
Orientation	Coronal
Rotation	0.00 deg
F >> H	150 mm
R >> L	150 mm
A >> P	79 mm

Physio

1st Signal/Mode	None
-----	
Dark blood	Off
-----	
Resp. control	Off

Inline

Subtract	Off
Std-Dev-Sag	Off
Std-Dev-Cor	Off
Std-Dev-Tra	Off
Std-Dev-Time	Off
MIP-Sag	Off
MIP-Cor	Off
MIP-Tra	Off

# SIEMENS MAGNETOM Product syngo MR B17

MIP-Time	Off
Save original images	On

---

## Sequence

Introduction	On
Dimension	2D
Compensate T2 decay	Off
Reduce Motion Sens.	Off
Contrasts	1
Bandwidth	180 Hz/Px
Flow comp.	No
Allowed delay	30 s
Echo spacing	11.5 ms

---

Define	Turbo factor
Turbo factor	4
Echo trains per slice	132
RF pulse type	Normal
Gradient mode	Fast