

www.siemens.com/diagnostics

AD VIA[®] Chemistry XPT System^{*}

Technical Specifications

Product Specifications

System Description	Fully random and continuous access, discrete processing clinical chemistry system with batch run capability
Test Throughput	Up to 2400 tests/hour: 1800 tests/hour photometric, 600 tests/hour ISE
Assays Onboard	59 assays, including 3 ISE (Na, K, Cl)

Sample Handling

Sample Tubes	5 mL, 7 mL, and 10 mL tubes; 1 mL and 2 mL sample cups; user-defined containers
Sample Tray	84 sample positions; positive sample identification
Validated Sample Types	Serum, plasma, urine, whole blood, and CSF, assay-dependent
Sample Integrity Control	Qualitative check for hemolysis, lipemia, and icterus; clot detection, flagging, and management; short-sample detection, flagging, and management
STAT Handling	84 positions, not dedicated; STAT samples are processed with priority
Auto-repeat Testing	Automatic repeat testing from the retained prediluted sample or original sample
Sample Dilution	Automatic dilution up to 1:5625 from retained prediluted sample or original sample
Auto-reflex Testing	Automatic ability to perform additional tests based on results of first test or test combination
Primary Sample Probe	Liquid-level sensing, crash protection, clot/clog detection, liquid-surface verification
Sample Carryover Prevention	Automated wash; additional automated sample probe washes programmable for greater prevention
Sample Throughput	Up to 200 tubes per hour with ISE use; faster without ISE use

Bar Codes

Sample Bar Codes	Up to 20 digits; Interleaved 2 of 5, Code 39, Code 128, Codabar; A, B, and special characters (-/+/*\$%)
-------------------------	--

Micro-volume Technology

Automatic Sample Predilution	Samples typically diluted 1:5 (30 µL sample + 120 µL saline generates up to 15 tests results); retained for auto-repeat, auto-reflex, or auto-dilution until results are available
Predilution Tray	120 dilution cuvettes
Sample Volume per Test	2–30 µL of prediluted sample, equating to 0.4–6.0 µL of original sample per test (varies by assay)
Average Reagent Volume	80–120 µL per test, assay-dependent

Reaction Area

Reaction Cuvettes	340 reusable optical-grade plastic cuvettes
Reaction Bath	Inert fluorocarbon oil circulation system, 37°C
Photometer	14 fixed wavelengths (340, 410, 451, 478, 505, 545, 571, 596, 658, 694, 751, 805, 845, and 884 nm)
Light Source	12V, 50W halogen lamp, cooled by forced water circulation
Assay Result Calculations	Endpoint (EPA), rate reaction (RRA), 2-point rate (2PA), constant rate analysis (CRA), and immunoassay analysis (IMA) methodologies; prozone checking; substrate depletion check; results available as completed
Reaction Times	3, 4, 5, and 10 minutes; extended reaction times 15 and 21 minutes
Automatic Correction	Sample blank, cuvette blank, measurement point change, sample volume change in re-assay
Point Forwarding	Can automatically extend linearity to measure samples over assay range
Assay Technology	Potentiometric, photometric, turbidimetric

Reagent Handling

Reagent Tray	2 trays, (R1=60 and R2 =56 positions), refrigerated between 6°C and 13°C (43°F–55°F)
Reagent Capacity Onboard	56 photometric assays
Test Capacity Onboard	40,000 photometric tests average; over 100,000 photometric tests with the use of concentrated reagents
Reagent Containers	20, 40, 70 mL reagent wedges
Reagent Integrity Control	Bar-code reagent identification; automatic inventory tracking and flagging; calibration and control validity tracking and flagging; reagent onboard stability tracking and flagging; reagent expired/reagent low flagging
Onboard Stability	Up to 60 days, depending on assay
Reagent Dilutions	Capability to dilute concentrated reagents onboard

* Due to local regulations, not all products are available in all countries.

ADVIA Chemistry XPT System*

Open-system Capability

Channels 200 assay channels; includes 50 channels for user-defined applications

Ion-selective Electrodes (ISE)

ISE Indirect simultaneous measurement of Na⁺, K⁺, Cl⁻

ISE Sample Volume 22 µL original sample for all three tests

Electrode Expected Use Life 30,000 samples or 3 months, whichever occurs first

Throughput Rate Up to 600 tests/hour; 200 tubes/hour

Calibration/QC

Validated Calibration Interval Up to 60 days, tracked by software

Auto-calibration User-defined time interval or with new reagent container

Auto-QC User-defined test count interval or with auto-calibration

View Calibration Graphical display of calibration curves

QC Data Graphical display of QC; real-time/QC monitoring; Advanced QC package includes Levey-Jennings plots, Westgard rules, and RiliBÄK rules; 125,000 control results can be stored, archivable to removable media

Calibration/Control Tray 61 refrigerated positions for calibrators, controls, and diluents

User Interface/Data Management

Monitor 22-inch (55.9 cm) diagonal high-resolution LCD touchscreen with adjustable height

Operating System Microsoft® Windows® 7

System Documentation Operator manual, quickstart guide, and online help

Data Storage 500,000 active plus 500,000 historical test results; can archive to removable media

Onboard Maintenance Logs Yes

Host Interface TCP/IP bidirectional

Host Query ASTM; system requests work order or batch of work orders from host

Remote Access and Service Siemens Remote Service via 1000BASE-T Ethernet port

Removable Media

Removable Media DVD, CD-RW, or USB

General Specifications

Power Requirements 200–240V at 50/60 Hz, 3 kVA consumption

Water Requirements CLSI® Clinical Laboratory Reagent Water or equivalent connected directly to a pressurized water source

Maximum Water Consumption 40 liters (10.6 gallons) per hour

Drain Requirements Minimum of 40 liters (10.6 gallons) per hour

Dimensions With monitor: 149 (h) x 177 (w) x 99 (d) cm; 59 (h) x 70 (w) x 39 (d) inches
Without monitor: 134 (h) x 177 (w) x 99 (d) cm; 53 (h) x 70 (w) x 39 (d) inches

Weight 725 kg (1598 lb)

Compliance Complies with international environmental, health, and safety standards, including CE and RoHS

Noise Emission Less than 62 dB

Processing Heat Output 5374 BTU/hour

Ambient Temperature 18°–30°C (64°–86°F)

Ambient Humidity 20–80% noncondensing

*Due to local regulations, not all products are available in all countries.

Siemens Healthcare Diagnostics, a global leader in clinical diagnostics, provides healthcare professionals in hospital, reference, and physician office laboratories and point-of-care settings with the vital information required to accurately diagnose, treat, and monitor patients. Our innovative portfolio of performance-driven solutions and personalized customer care combine to streamline workflow, enhance operational efficiency, and support improved patient outcomes.

ADVIA and all associated marks are trademarks of Siemens Healthcare Diagnostics Inc. All other trademarks and brands are the property of their respective owners.

Product availability may vary from country to country and is subject to varying regulatory requirements. Please contact your local representative for availability.

Global Siemens Headquarters

Siemens AG
Wittelsbacherplatz 2
80333 Muenchen
Germany

Global Siemens Healthcare Headquarters

Siemens AG
Healthcare Sector
Henkestrasse 127
91052 Erlangen
Germany
Telephone: +49 9131 84 - 0
www.siemens.com/healthcare

Global Division

Siemens Healthcare Diagnostics Inc.
511 Benedict Avenue
Tarrytown, NY 10591-5005
USA
www.siemens.com/diagnostics

Order No. A91DX-CAI-140251-GC1-4A00
06-2014 | All rights reserved
© 2014 Siemens Healthcare Diagnostics Inc.